



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-20-100585	20OCT2020	S.K	D.Z

D

C

B

A



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.60 [.063] THICK PC BOARD

- 1

HOUSING MATERIAL: NYLON, UL94 V0.
- 2

PIN MATERIAL: BRASS.
- 3

PIN PLATING: 0.003 [.000120] MIN TIN OVER
0.001 [.000039] MIN NICKEL.
- 4

2 POSITION HAS 1 PEG, ALL OTHERS HAVE 2 PEGS.
- 5

PARTS MEETS IEC 60335-1 GWT (GLOW WIRE TEST)
750°C SPEC.
- 6

SKETCHES SHOW NO PINS MISSING.
- 7

"O" WITH PIN
"X" WITHOUT PIN.

O	X	O	X	O	X	O			7	NATURAL	27.72	[1.091]	1-1744429-7
O	X	O	O	X	O				6	NATURAL	23.76	[0.935]	2-1744429-6
O	O	X	O	O	O	O	O	O	9	NATURAL	35.64	[1.403]	1-1744429-9
O	O	X	O	O	O				6	NATURAL	23.76	[0.935]	1-1744429-6
O	X	O	O						4	NATURAL	15.84	[0.624]	1-1744429-4
O	X	O	X	O					5	NATURAL	19.80	[0.780]	1-1744429-5
O	X	O							3	NATURAL	11.88	[0.468]	1-1744429-3
O	O	O	O	O	O	O	O	O	9	NATURAL	35.64	[1.403]	1744429-9
O	O	O	O	O	O	O	O		8	NATURAL	31.68	[1.247]	1744429-8
O	O	O	O	O	O	O			7	NATURAL	27.72	[1.091]	1744429-7
O	O	O	O	O	O				6	NATURAL	23.76	[0.935]	1744429-6
O	O	O	O	O					5	NATURAL	19.80	[0.780]	1744429-5
O	O	O	O						4	NATURAL	15.84	[0.624]	1744429-4
O	O	O							3	NATURAL	11.88	[0.468]	1744429-3
O	O								2	NATURAL	7.92	[0.312]	1744429-2
1	2	3	4	5	6	7	8	9	NO. OF POSITIONS	COLOR	mm	IN	PART NUMBER
PIN POSITIONS 											DIM A ±0.30		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	± 0.5 [.020]
2 PLC	± 0.30 [.012]
3 PLC	± -
4 PLC	±
ANGLES	±
FINISH	

DWN
JR RUTH
09JAN12

CHK
SAM MACE
09JAN12

APVD
SAM MACE
09JAN12

PRODUCT SPEC
108-5609

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
HEADER ASSEMBLY-ECONOMY POWER
VERTICAL, W/RETENTION PEGS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1744429

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 1

REV
D1