




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4106-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4106-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
3. EYELET FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
3. PART MARKING: STANDARD PART: NO MARKING. RoHS PART: GREEN DOT IDENTIFIER.

MIN. CAP (pF)	WORKING VOLTAGE (WVDC)		CURRENT Idc	I.R. MIN. @ 100 (VDC)	DWV	MINIMUM NO-LOAD INSERTION LOSS			
	85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
3000	500 DC 350 AC	500 DC 350 AC	25A	10 G	1250 VDC	----	50	50	50

X-2015 Rev-0	REVISION RECORD		Original Release C.O. 20040219-2-01 ADDED NOTES 1-4. S.M. 07-26-05 20050718-3-02			--TOLERANCES-- Unless Otherwise Specified		Title EYELET STYLE EMI FILTER		
	0					DECIMAL ±				
						ANGLES ±	Drawn	L.E. 02-19-04	Scale	3 X
	1					TUSONIX TUCSON, ARIZONA	Approved			T.C. 02-19-04
							A	4106-000		