






N = Number of poles
 Dim A = $N \times 9.5 + 1.5$
 Dim B = $(N - 1) \times 9.5$

Poles	Tol.	Dim A & B
2-4p		± 0.20
5-8p		± 0.25
9-16p		± 0.35
17-23p		± 0.40
24-30p		± 0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'08	Add APPROVAL: CQC	Kind
△	4/17'09	Explanation changed	Eris
△	06/04'11	Critical dimension is changed.	Tason
△	06/04'11	The Wire Range is changed from 20-14AWG to 22-14AWG	Tason
△	06/04'11	The tolerance table is changed.	Tason
△	06/16'11	The dimension is changed from 5.56 to 5.5	Tason
△	06/16'11	The dimension is changed from 1.6 to 1.5	Tason
△	11/10'12	Change the screw plating specification	Jacky
△	12/23'13	Change the withatand voltage , current, Screw Torque.	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- MATERIALS ELECTRICAL
- △ 2 RATED VOLTAGE & CURRENT: cULus / CQC 300 V, 30A / 300V 24A △ 9
 - WITHSTAND VOLTAGE: AC2500V/min △
 - INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 - OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 - SCREW TORQUE VALUE: 10.54 Lb-In. / 0.8Nm △ 9
 - △ 2 WIRE RANGE: 22 - 10 AWG / 22-14 AWG △
 - 1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK
 - 2) TERMINAL: BRASS, 0.8t, Tin PLATED
 - △ 8 3) TERMINAL SCREWS: STEEL, M3.5
 - 4) Flange: Thermoplastic, UL 94 V-0 BLACK
 - △ 3 Critical dimension: △
 - △ 1 APPROVAL: △

YK 443 xx 3 x x 00G G:RoHS compliant (lead<4%) in copper alloy
 MARK 0: "@" MARK 1: "ANY" MARK

- NO. OF POLES
- 02: 2 POLES
 - 03: 3 POLES
 - 04: 4 POLES
 - ...
 - 30: 30 POLES
- △ 8 1: TERMINAL & SCREW: G/F
 2: TERMINAL: Sn, SCREW: G/F
 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		YK-443 Series		DWG NO.		8YK0001-443	
PART NO.		YK443xx3xx00G		DWG NO.		8YK0001-443	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Guoxue 2014.01.07	Guoxue 2014.01.07		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°		
SHEET: 01/01				UNIT: mm SCALE: NONE REV.: J			