

1. MATERIAL :



HOUSING - THERMOPLASTIC, GLASS PREINFORCED, COLOR, BLACK, UL 94V-0
CONTACTS- COPPER ALLOY.

2. FINISH:

MATING AREA - NOBLE METAL OVERALL NICKEL.

SOLDER TAIL - MATTE TIN OVERALL NICKEL.

3 MARK P/N AND DATA CODE IN APPROX. AREA AS SHOWN.





CONNECTOR ACCEPTS
1.6±0.14 mm PCB

SECTION AC-AC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 01SEP2017 SEAN ZHANG CHK		PART NUMBER 8222260-1	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.0 1 PLC ±.0 .40 2 PLC ±.0 .20 3 PLC ±.0 .10 4 PLC ±. ANGLES ±.2 FINISH		APVD 01SEP2017 SUNY ZHAO PRODUCT SPEC 108-128060 APPLICATION SPEC - WEIGHT -	
MATERIAL -		CUSTOMER DRAWING		NAME HIGE DENSITY HYBRID POWER CARD EDGE SOLDER TYPE LOW PROFILE SIZE CASE CODE DRAWING NO A 00779 © 8222260 RESTRICTED TO -	
		SCALE 1:1 SHEET 1 OF 2 REV A			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	-	-	SEE SHEET 1	-	-	-



NOTES FOR MOUNTING BOARD,UNLESS OTHERWISE SPECIFIED:

- 1.PLATED THROUGH HOLE, SIGNAL:
FINISHED HOLE SIZE:0.85mm.
DRILL HOLE SIZE:0.95±0.025mm.
- 2.PLATED THROUGH HOLE, POWER:
FINISHED HOLE SIZE:1.2mm.
DRILL HOLE SIZE:1.3±0.025mm.
- 3.COPPER PLATING THICKNESS:0.025~0.05mm.
- 4.SURFACE FINISH:OSP OR IMMERSION TIN PLATING
IS RECOMMENDED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SEAN ZHANG CHK	01SEP2017	 TE Connectivity		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				
mm		APVD: SUNY ZHAO 01SEP2017		NAME HIGE DENSITY HYBRID POWER CARD EDGE SOLDER TYPE LOW PROFILE		
		PRODUCT SPEC 108-128060				
		APPLICATION SPEC		SIZE A100779		
MATERIAL		WEIGHT				
-		-		DRAWING NO: C=2322260		
				RESTRICTED TO -		
CUSTOMER DRAWING				SCALE 1:1 SHEET 2 OF 2 REV A		