



THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.
IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	.02	W
MAX INPUT POWER	.03	W
IMPEDANCE	$32 \pm 15\%$	OHM
OUTPUT SPL @ 1.0 kHz, 1cm, 1mW	115 ± 3	dBA
DISTORTION (MAX.)	5%	—
FREQUENCY RANGE	60 ~ 10,000	Hz
HOUSING MATERIAL	ABS	—
CONE MATERIAL	MYLAR	—
MAGNET MATERIAL	NdFeB	—
OPERATING TEMPERATURE	$-20 \sim +60$	°C
WEIGHT	5.8	grams



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL
WITHOUT NOTICE.
3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

FILE NAME: AR03032MR-R.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ± 0.5 AND
ANGLES ARE $\pm 3^\circ$.

APPROVALS	DATE
DRAWN J.D.	3/12
CHECKED M.L.	4/12
APPROVED B.R.	4/12



3541 Stop Eight Road
Dayton, Ohio 45414

RECEIVER		DRAWING NO.	SCALE: N.T.S.	SHEET 1 OF 1
AR03032MR-R				