


DASH NO.	M CODE	MADE FROM
----------	--------	-----------

GSD

2029-15-9

REVISIONS	
ISSUE	CHANGES
0	ER 32981 JCA 03/20/91
1	CN 35329 C KVH 02/16/94
2	CN 38020 C TML 06/12/00
2029159S	



- NOTES:
- INTERFACES PER MIL-STD-348, FIG. 301-2 (AS APPLICABLE)..
 - MATERIALS:
INSULATOR: TEFLON, ASTM-D-4894
CENTER CONTACT: BER. COP., ASTM-B-196
ALL OTHER PARTS: BRASS, ASTM-B16
 - FINISHES:
CENTER CONTACT : HARD GOLD PLATE PER MIL-STD-45204
ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
 - ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE: 75 OHMS
VOLTAGE RATING: 500 VRMS
FREQUENCY RANGE: DC TO 2 GHz

- | | | |
|---|--|---|
| UNLESS OTHERWISE SPECIFIED | | |
| 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010 | 2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX. | 7. ALL LEAD THREADS TO BE CHAMFERED 45° TO ROOT DIAMETER. |
| 3 PLACE DECIMALS ± .004 ANGLES ± 1° | 3. NO FILLETS PERMITTED. | ★ CRITICAL DIMENSIONS |
| CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES. | 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX. | |
| | 5. ALL DIMENSIONS PRIOR TO PLATING. | |
| | 6. ALL PLATING IN ACCORDANCE WITH KER 10004. | |

GSD

SCALE 4:1	
APPROX SURFACE AREA	
WAS: JCA1498	
USED ON	
REF:	
ADPT, F-F, 75 BNC-75 BNC	
DRAWN JCA	DATE 03/20/91
DESIGN GA	DATE 03/21/91
APPR.	DATE
 KINGS ELECTRONICS CO., INC. ROCK HILL, SOUTH CAROLINA 29730	
2029-15-9	