

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

G

14

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------

A

DRAWN PER ECR 07-020029


22AUG07

	JR
--	----

	TM
--	----


AMP
WIRE RANGE

22 AWG
SOLID OR STRANDED



- 1 STAMP AMP 22, LOCATE APPROX AS SHOWN.
- 2 WIRE INSULATION DIA IS 0.9-2.5 [0.035-.100]
- 3 TONGUE MATERIAL THK IS 0.79±0.05 [0.031±0.002]
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5 MATERIAL: BODY-COPPER PER ASTM B-152
SLEEVE-NYLON, BLACK
- 6 FINISH: BODY-TIN PLATE PER ASTM B-545
- 7 MAX RECOMMENDED OPERATING 105°C
- 8 VOLTAGE RATING 300V MAX
- 9 CIRCULAR MIL AREA 0.26-0.41mm² [509-810] CMA.

500	LOOSE PIECE	151458
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 22AUG07		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		CHK T MICHIELUTTI 22AUG07		TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 22 AWG —	
		APVD T MICHIELUTTI 22AUG07			
		PRODUCT SPEC —			
		APPLICATION SPEC —		SIZE	CAGE CODE
MATERIAL		FINISH		DRAWING NO	
				RESTRICTED T	
CUSTOMER DRAWING				SCALE	REV
				8.1	1 OF 1