


3	PBT	(BLACK) UL94V-0	6	BRASS 	TIN PLATING
2	PBT	(BLACK) UL94V-0	5	PHOSPHOR BRONZE	NICKEL PLATING
1	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.2µ m	4	STEEL	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

 SCALE 2 : 1	DRAWING NO.	PART NO.
	EDC3-045357-01  HIROSE ELECTRIC CO., LTD	DX10GM-68SE(50) CODE NO. CL230-5134-2-50



Technical drawing of a mechanical part (Fig. 1) showing a cross-section. The drawing includes the following dimensions and tolerances:

- Top horizontal dimension: 54.23 ± 0.1
- Bottom horizontal dimension: 57.93 ± 0.1
- Left vertical dimension: $R1.5 \pm 0.1$
- Right vertical dimension: 8.1 ± 0.1

PANEL CUTOUT (SCALE 1/1)
(PANEL THICKNESS TO BE 1.6 mm MAX)

