








## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERM. NUMBERS FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 160  $\pm 50$ gf
6. TRAVEL: 0.2mm  $\pm 0.1$
7. CONTACT RESISTANCE: 500 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 160g > 100,000 CYCLES
9. SILVER CONTACTS
10. PACKAGING: TAPE & REEL; 1000 PIECES PER REEL.
11. ▲ DENOTES CRITICAL PARAMETER

CIRCUIT: SPST  
SCHEMATIC

| REV                                                                                                          | ECO NO     | DESCRIPTION                         | DATE     | BY | E-SWITCH®           |           |    |         | OBJECT ID |
|--------------------------------------------------------------------------------------------------------------|------------|-------------------------------------|----------|----|---------------------|-----------|----|---------|-----------|
| B                                                                                                            | ECO-101525 | NOTE 10 1000 PIECES WAS 2000 PIECES | 12/27/22 | JS | TITLE TL3340BF160QG |           |    |         | 100121867 |
| A                                                                                                            | ECO-100947 | Release                             | 05/18/22 | MW |                     |           |    |         |           |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |            |                                     |          |    | SCALE               | DATE      | DR | DWG     | REV       |
|                                                                                                              |            |                                     |          |    | 6:1                 | 4/28/2022 | MW | P021303 | B         |