








△ N = Number of poles
 Dim L=(N×5.08)+2.54
 Dim P=(N-1)×5.08

	Dim L	Dim P
1p	±0.10	±0.10
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30



△ P.C.B. LAYOUT
 Bottom view

SIGN	DATE	DESCRIPTION	APPROVER
△	01/20'07	The Soldering temperature from 245° to 250°	Aaron
△	2010.08.12	The design is changed	Chen Bo
△	2012.07.18	The tolerance are added	Runner
△	10/29'12	update the drawing	Da cheng
△	2015.09.29	Update the drawing	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Lever: Thermoplastic (UL94V-0) Orange RAL2011/P
- Item ② Terminal body: Thermoplastic (UL94V-0)
- Item ③ cover: Thermoplastic (UL94V-0)
- Item ④ Spring clamp: Stainless steel
- Item ⑤ contact pin: Brass. Bright Tin plated over Nickel plated

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus VDE
- Critical dimension: ∇

HA xx 00 x 0 xxxx G

△ 01 1 Poles
 02 2 Poles
 ...
 24 24 Poles

△ Body color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 5 Green(RAL6018/T)
 8 Grey(RAL7004/P)
 9 White(RAL1102)
 C Multiple colors

RoHS compliant (lead<4%)
 In copper Alloy
 0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HA-5.08mm 90° series							
PART NO.	HAxx00x0xxxxG			DWG NO.	8HA0101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Airy min 2015.09.29	Airy min 2015.09.29				UNIT: mm	X.
					SCALE: NONE		X.X	±0.30
					REV.: G		X.XX	±0.10
							X°	±1°