






1. .000100 MIN BRIGHT TIN—LEAD OVER .000050 MIN NICKEL ON ENTIRE CONTACT
2. .000050 MIN NICKEL ON ENTIRE CONTACT; .000015 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
3. .000050 MIN NICKEL ON ENTIRE CONTACT; .000030 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
4. LOOSE PIECE CUT—OFF DIMENSION.
5. .000015 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
6. .000030 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
8. .000100 MIN TIN OVER .000050 MIN NICKEL ON ENTIRE CONTACT

	LOOSE PIECE		REF	5-104481-6
	STRIP			5-104481-2
	LOOSE PIECE		REF	1-104481-3
	LOOSE PIECE		REF	1-104481-2
	STRIP			1-104481-1
	STRIP			1-104481-0
OBSOLETE	LOOSE PIECE			104481-9
	LOOSE PIECE		REF	104481-8
	LOOSE PIECE		REF	104481-7
	LOOSE PIECE		REF	104481-6
OBSOLETE	STRIP			104481-5
	STRIP			104481-4
	STRIP			104481-3
	STRIP			104481-2
	REMARKS		FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG C. OBERMAN	0-10-89				
						CHK K. HELM	0-12-89	 TE Connectivity			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVED R. FICKLER		NAME		CONTACT, CRIMP SNAP-IN AMPMODU SHORT POSITION, 28-32 AWG			
		Ø PLCS ± .-		PRODUCT SPEC				DRAWING NO			
		PLCS ± .-		108-1472							
		PLCS ± .005		APPLICATION SPEC							
MATERIAL PHOSPHOR BRONZE		FINISH SEE TABLE		WEIGHT -		SIZE A1		CAGE CODE 00779	DRAWING NO C=104481	RESTRICTED TO -	
						CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1	REV. N