

Bandpass Filter

50Ω 120 to 150 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W at 25°C
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

RF IN	2
RF OUT	6
GROUND	1,3,4,5,7,8

Outline Drawing





Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R	wt	
.050	.040	.195	.390	.120	.390	.070	grams	
1.27	1.02	4.95	9.91	3.05	9.91	1.78	0.25	

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



Features

- high rejection
- linear phase, up to ±6deg typ. @ Fc ±15MHz
- good VSWR, 1.3:1 typ. @ passband
- small size 0.35" x 0.35"
- shielded case
- aqueous washable


Applications

- harmonic rejection
- transmitters / receivers
- base station


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz) Fc	PASSBAND (MHz) (Loss < 3.5dB) F1 - F2	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.) Fc ± 15MHz	VSWR (:1)		
		Loss > 20dB		Loss > 35dB			Passband		Stopband
		F3	F4	F5	F6		Typ.	Max.	Typ.
135	120 - 150	85	210	75	245-2000	±12	1.3	1.8	18

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg)
1.0	90.55	9035.28	120.0	5.81
40.0	90.05	868.59	122.0	3.74
75.0	45.52	91.43	123.0	2.89
85.0	33.18	43.44	125.0	1.54
95.0	18.74	14.50	127.0	0.57
100.0	10.53	5.47	129.0	-0.11
104.0	5.28	1.93	130.0	-0.35
120.0	2.26	1.28	131.0	-0.55
135.0	2.01	1.09	133.0	-0.80
150.0	2.28	1.39	135.0	-0.89
170.0	4.81	2.24	137.0	-0.84
177.0	9.12	4.79	140.0	-0.54
210.0	31.97	29.46	143.0	-0.05
245.0	45.60	56.04	145.0	0.34
500.0	74.19	133.63	147.0	0.70
1000.0	74.95	72.39	149.0	1.00
2000.0	60.33	45.72	150.0	1.10



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



RBP-135+



Generic photo used for illustration purposes only

CASE STYLE: GP731

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000