



PANEL CUTOUT

| PANEL THICKNESS | (x)  | TOLERANCE |
|-----------------|------|-----------|
| 0.75 - 1.25 mm  | 30.0 | +0.1/-0   |
| 1.25 - 2.00 mm  | 30.2 | +0.1/-0   |
| 2.00 - 3.00 mm  | 30.5 | +0.1/-0   |





| SWITCH FUNCTION |        |        |
|-----------------|--------|--------|
| POS. 1          | POS. 2 | POS. 3 |
|                 |        |        |
| ON              | OFF    | ON     |
| 2-3             | OPEN   | 2-1    |



CIRCUIT DPST

## NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
- ▲ 5. CONTACT RATINGS: 16A @ 125/250VAC [cURus]
6. CONTACT RESISTANCE: 20m $\Omega$  MAX. INITIAL
7. INSULATION RESISTANCE: 100M $\Omega$  MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [cURus]
10. OPERATING TEMPERATURE: -20°C TO 55°C [cURus]
11. ▲ DENOTES CRITICAL PARAMETER



| REV | ECO NO     | DESCRIPTION                     | DATE     | BY | E-SWITCH®        |           |    |               | OBJECT ID |
|-----|------------|---------------------------------|----------|----|------------------|-----------|----|---------------|-----------|
| B   | ECO-100695 | REMOVE VED/ENEC RATING AND LOGO | 01/27/22 | JS | TITLE RB145E1900 |           |    |               | 000000290 |
|     |            |                                 |          |    | SCALE            | DATE      | DR | DWG           | REV       |
|     |            |                                 |          |    | 1:1              | 2/24/2016 | MW | 14-RB145E1900 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED