

High Current Ferrite Bead


BPH403025R5-530T

1. Features


- 100% Lead(Pb) & Halogen-Free and RoHS compliant.
- Operating temperature-40~+125°C (Including self - temperature rise)



2. Dimension



CORE SIZE			
A(mm)	B(mm)	C(mm)	D(mm)
4.00±0.25	3.10±0.15	2.50±0.15	1.50±0.15



PRODUCT SIZE				
A(mm)	B(mm)	C(mm)	D(mm)	E(mm)
4.30~5.10	3.10±0.15	2.70~3.10	1.35±0.20	1.35±0.15

3. Part Numbering

BPH
403025
R5
-
530
T

A

B

C

D

E

A: Series

B: Dimension

C: Material

Ferrite Core

D: Impedance

530=53Ω

E: Packaging

T=Taping and Reel

4. Specification

TAI-TECH Part Number	ELECTRICAL REQUIREMENTS 1			ELECTRICAL REQUIREMENTS 2			DCR (mΩ) Max.	Rated Current(A)	
	Impedance (Ω)	Tolerance (%)	Test Frequency (MHz)	Impedance (Ω)	Tolerance (%)	Test Frequency (MHz)		ΔT=40°C TYP.	ΔT=60°C TYP.
BPH403025R5-530T	35	±25	25	53	±25	100	0.60	35.0(1) 15.0(2)	45.0(1) 18.0(2)


Note:

Rated Current :


(1) : Chroma high current test fixture.

(2) :PCB test fixture (30x45mm copper pattern , 50um copper thickness).

Typical Impedance v.s. Frequency Curve



5. Recommended PC Board Pattern



L(mm)	G(mm)	H(mm)
4.8	1.4	1.5