

# Frequency Mixer

## Level 7 (LO Power +7 dBm) 300 to 4000 MHz

## ADE-30W+



Generic photo used for illustration purposes only

CASE STYLE: CD542

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel     |
|-----------|------------------|
| 7"        | 20, 50, 100, 200 |
| 13"       | 500, 1000        |

### Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power              | 50mW           |
| IF Current            | 40mA           |

Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

|        |       |
|--------|-------|
| LO     | 6     |
| RF     | 3     |
| IF     | 2     |
| GROUND | 1,4,5 |

### Outline Drawing



#### PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

### Outline Dimensions (inch)

| A    | B    | C    | D    | E    | F    | G    |       |
|------|------|------|------|------|------|------|-------|
| .272 | .310 | .220 | .100 | .112 | .055 | .100 |       |
| 6.91 | 7.87 | 5.59 | 2.54 | 2.84 | 1.40 | 2.54 |       |
| H    | J    | K    | L    |      |      |      | wt    |
| .030 | .026 | .065 | .300 |      |      |      | grams |
| 0.76 | 0.66 | 1.65 | 7.62 |      |      |      | 0.20  |

### Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- low conversion loss, 6.8 dB typ.
- excellent L-R isolation, 35 dB typ.
- low profile package
- aqueous washable
- protected by U.S. patent 6,133,525

### Applications

- cellular
- PCN
- instrumentation
- ISM

### Electrical Specifications


| FREQUENCY (MHz)      | CONVERSION LOSS (dB)                                      | LO-RF ISOLATION (dB) | LO-IF ISOLATION (dB) | IP3 at center band (dBm) |
|----------------------|-----------------------------------------------------------|----------------------|----------------------|--------------------------|
|                      |                                                           |                      |                      |                          |
| LO/RF<br>$f_L - f_U$ | Mid-Band<br>m<br>$\bar{X}$ $\sigma$ Max. Total Range Max. | Typ. Min.            | Typ. Min.            | Typ.                     |
| 300-4000 DC-950      | 6.8 0.20 9.0 9.8                                          | 35 17                | 16 7                 | 12                       |







1 dB COMP: +1 dBm typ.  
m= mid band [ $2f_L$  to  $f_U/2$ ]

### Typical Performance Data

| Frequency (MHz) |         | Conversion Loss (dB) | Isolation L-R (dB) | Isolation L-I (dB) | VSWR RF Port (:1) | VSWR LO Port (:1) |
|-----------------|---------|----------------------|--------------------|--------------------|-------------------|-------------------|
| RF              | LO      | LO +7dBm             | LO +7dBm           | LO +7dBm           | LO +7dBm          | LO +7dBm          |
| 200.00          | 230.00  | 5.93                 | 51.00              | 48.50              | 2.80              | 8.08              |
| 350.00          | 380.00  | 4.87                 | 45.33              | 40.83              | 1.43              | 6.17              |
| 500.00          | 530.00  | 4.84                 | 42.83              | 37.83              | 1.13              | 3.26              |
| 850.00          | 880.00  | 5.24                 | 38.17              | 45.00              | 2.46              | 2.51              |
| 1050.00         | 1080.00 | 6.02                 | 38.50              | 34.67              | 3.69              | 2.04              |
| 1250.00         | 1280.00 | 5.80                 | 40.67              | 23.67              | 2.51              | 1.95              |
| 1450.00         | 1480.00 | 5.34                 | 38.50              | 19.00              | 2.20              | 2.17              |
| 1650.00         | 1680.00 | 6.12                 | 40.83              | 15.66              | 2.28              | 2.28              |
| 1850.00         | 1880.00 | 6.38                 | 40.00              | 14.77              | 2.46              | 2.37              |
| 2000.00         | 2030.00 | 6.66                 | 39.00              | 13.50              | 2.86              | 2.51              |
| 2250.00         | 2280.00 | 7.17                 | 35.50              | 12.83              | 3.68              | 2.93              |
| 2450.00         | 2480.00 | 6.79                 | 33.67              | 12.00              | 3.57              | 3.17              |
| 2650.00         | 2680.00 | 6.39                 | 37.00              | 11.16              | 3.68              | 3.36              |
| 2850.00         | 2880.00 | 5.69                 | 40.67              | 10.50              | 2.86              | 3.95              |
| 3000.00         | 3030.00 | 5.30                 | 37.17              | 11.17              | 2.01              | 3.17              |
| 3250.00         | 3280.00 | 5.16                 | 34.00              | 12.16              | 1.65              | 2.07              |
| 3450.00         | 3480.00 | 5.27                 | 33.33              | 14.50              | 1.43              | 2.20              |
| 3650.00         | 3680.00 | 5.75                 | 33.67              | 16.50              | 1.56              | 2.61              |
| 3850.00         | 3880.00 | 6.57                 | 33.66              | 17.00              | 2.61              | 3.17              |
| 4000.00         | 4030.00 | 7.38                 | 33.33              | 16.16              | 3.35              | 4.26              |

### Electrical Schematic





## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

