








PART NO.
20021321



SECTION A-A
SCALE 4.000



WITH CAP OPTION



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title					
M	ELX-N-24544	TONY	07/21/16	angles		.0±.30				RECEPTACLE VT SMT			
N	ELX-N-26833	TONY	03/14/17	linear		.00±.20							
P	ELX-N-29534	TONY	03/13/18	0°±2°		.000±.10							
R	ELX-N-38519-1	YY	10/10/20	dr	Tony Leng		07/19/16			dwg no		sheet 1 of 4	size
				engr	Y-Y Bao		10/10/20			20021321		A3	
				chr	L-Q Lei		10/10/20						
				appd	Tim Yao		10/10/20						
sheet index	revision sheet	R	1							type	Product	Customer	Drawing



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AFCE

© 2016 AFCE

D



B

C

D

© 2016 AF

TABLE 1

PRODUCT NO.	POSITIONS	DIM. A	DIM. B
20021321-X0X06XXLF	2 X 3	2.54	4.27
20021321-X0X08XXLF	2 X 4	3.81	5.54
20021321-X0X10XXLF	2 X 5	5.08	6.81
20021321-X0X12XXLF	2 X 6	6.35	8.08
20021321-X0X14XXLF	2 X 7	7.62	9.35
20021321-X0X16XXLF	2 X 8	8.89	10.62
20021321-X0X18XXLF	2 X 9	10.16	11.89
20021321-X0X20XXLF	2 X 10	11.43	13.16
20021321-X0X22XXLF	2 X 11	12.7	14.43
20021321-X0X24XXLF	2 X 12	13.97	15.7
20021321-X0X26XXLF	2 X 13	15.24	16.97
20021321-X0X28XXLF	2 X 14	16.51	18.24
20021321-X0X30XXLF	2 X 15	17.78	19.51
20021321-X0X32XXLF	2 X 16	19.05	20.78
20021321-X0X34XXLF	2 X 17	20.32	22.05
20021321-X0X36XXLF	2 X 18	21.59	23.32
20021321-X0X38XXLF	2 X 19	22.86	24.59
20021321-X0X40XXLF	2 X 20	24.13	25.86
20021321-X0X42XXLF	2 X 21	25.4	27.13
20021321-X0X44XXLF	2 X 22	26.67	28.4
20021321-X0X46XXLF	2 X 23	27.94	29.67
20021321-X0X48XXLF	2 X 24	29.21	30.94
20021321-X0X50XXLF	2 X 25	30.48	32.21
20021321-X0X52XXLF	2 X 26	31.75	33.48
20021321-X0X54XXLF	2 X 27	33.02	34.75
20021321-X0X56XXLF	2 X 28	34.29	36.02
20021321-X0X58XXLF	2 X 29	35.56	37.29
20021321-X0X60XXLF	2 X 30	36.83	38.56
20021321-X0X62XXLF	2 X 31	38.1	39.83
20021321-X0X64XXLF	2 X 32	39.37	41.1
20021321-X0X66XXLF	2 X 33	40.64	42.37
20021321-X0X68XXLF	2 X 34	41.91	43.64

PRODUCT NO.	POSITIONS	DIM. A	DIM. B
20021321-X0X70XXLF	2 X 35	43.18	44.91
20021321-X0X72XXLF	2 X 36	44.45	46.18
20021321-X0X74XXLF	2 X 37	45.72	47.45
20021321-X0X76XXLF	2 X 38	46.99	48.72
20021321-X0X78XXLF	2 X 39	48.26	49.99
20021321-X0X80XXLF	2 X 40	49.53	51.26
20021321-X0X82XXLF	2 X 41	50.8	52.53
20021321-X0X84XXLF	2 X 42	52.07	53.8
20021321-X0X86XXLF	2 X 43	53.34	55.07
20021321-X0X88XXLF	2 X 44	54.61	56.34
20021321-X0X90XXLF	2 X 45	55.88	57.61
20021321-X0X92XXLF	2 X 46	57.15	58.88
20021321-X0X94XXLF	2 X 47	58.42	60.15
20021321-X0X96XXLF	2 X 48	59.69	61.42
20021321-X0X98XXLF	2 X 49	60.96	62.69
20021321-X0XA0XXLF	2 X 50	62.23	63.96

NOTES:

- MATERIAL:
HOUSING: HIGH TEMPERATURE PLASTIC; UL94-V0; BLACK.
TERMINAL: PHOSPHOR BRONZE.
CAP: STAINLESS STEEL.
- FINISH:
TERMINAL: GOLD OR GXT PLATING AT CONTACT AREA (SEE TABLE);
GOLD FLASH OR 2.54um/100u" MIN MATTE TIN
AT SOLDER TAIL AREA;
1.27um/50u" MIN NI OVER ALL AS UNDERPLATING.
- PRODUCT SPEC PER GS-12-629.
- PACKAGE SPEC PER GS-14-1420.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.
- THE METAL CAP IS OPTION AS CUSTOMER REQUIREMENT.

PART NUMBER DESCRIPTION:

20021321 - X 0 X X X X X LF

LEAD FREE

PLATING(SEE TABLE 2)

- GOLD FLASH ON CONTACT AREA; 100u" MATTE TIN ON SOLDER TAIL
- GOLD FLASH ON CONTACT AREA; GOLD FLASH ON SOLDER TAIL
- 10u" Au ON CONTACT AREA; 100u" MATTE TIN ON SOLDER TAIL
- 10u" Au ON CONTACT AREA; GOLD FLASH ON SOLDER TAIL
- 15u" GXT ON CONTACT AREA; 100u" MATTE TIN ON SOLDER TAIL
- 15u" GXT ON CONTACT AREA; GOLD FLASH ON SOLDER TAIL
- 30u" GXT ON CONTACT AREA; 100u" MATTE TIN ON SOLDER TAIL
- 30u" GXT ON CONTACT AREA; GOLD FLASH ON SOLDER TAIL

PACKAGE:

- T: TUBE
- D: TUBE + CAP
- C: TAPE & REEL + CAP
- V: DEDICATED FOR CUSTOMER, TAPE&REEL + CAP
- Q: TAPE&REEL WITHOUT CAP

PIN COUNT: (SEE TABLE 1)

- 06, 08, 10, ..., 98, A0
- (6 - 100 EVERY EVEN PIN)

SELECTED LOADED

- 0: FULLY LOADED, OTHER SEE SHEET 2 TABLE 3

POST:

- 0: WITHOUT POST
- 1: WITH POST STYLE 1
- 2: WITH POST STYLE 2
- 3: WITH POST STYLE 3

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®									
ltr ecn no dr date				tolerances unless otherwise specified						title									
				angles		linear		mm 		RECEPTACLE VT SMT									
				0±2°				.00±.10											
				dr		Tony Leng		07/19/16		dwg no sheet4 of 4 size									
				engr		Y-Y Bao		10/10/20											
				chr		L-Q Lei		10/10/20		20021321 A3									
				appd		Tim Yao		10/10/20											
sheet index		revision sheet		R		4													