

ETD Cores (9595494902)

Part Number: 9595494902

95 ETD CORE SET

ETD cores have been designed to make optimum use of a given volume of ferrite material for maximum throughput power, specifically for forward converter transformers. The structure, which includes a round center post, approaches a nearly uniform cross- sectional area throughout the core and provides a winding area that minimizes winding losses. ETD cores are used mainly in switched- mode power supplies and permit off- line designs where IEC and VDE isolation requirements must be met.

□ETD cores can be supplied with the center post gapped to a mechanical dimension or an A_L value.

[Catalog Drawing](#)
[3D Model](#)

Weight indicated is per pair or set.

Weight: 124 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	49	± 0.80	1.929	—
B	24.7	± 0.20	0.972	—
C	16.3	± 0.40	0.642	—
D	18.1	± 0.20	0.713	—
E	36.1	min	1.422	min
F	16.3	± 0.40	0.642	—




Chart Legend

$\Sigma l / A$: Core Constant, l_e : Effective Path Length, A_e : Effective Cross- Sectional Area, V_e :
Effective Core Volume
 A_L : Inductance Factor 

Explanation of Part Numbers: Digits 1 & 2 = product class and 3 & 4 = material grade.

Electrical Properties	
A_L (nH)	5700 ±25%
A_e (cm ²)	2.135
$\Sigma l / A$ (cm ⁻¹)	5.3
l_e (cm)	11.44
V_e (cm ³)	24.42
A_{min} (cm ²)	2.09

A_L value is measured at 1 kHz, B < 10 gauss