



- 1
- WIRE INSULATION: 12.70[.500] — 13.97[.550] DIA
- 2
- THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.



78.0 ^{±5} GRAMS	13.08 ^{±0.13} [.515 ^{±.005}]	1/2	77.47 [3.05]	18.03 [.71]	BODY: COPPER ASTM-B187 ANNEALED TIN PL PER MIL-T-10727 0.00381[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277152-5
81 ^{±5} GRAMS	9.91 ^{±0.13} [.390 ^{±.005}]	3/8				277152-4
80 ^{±5} GRAMS	8.33 ^{±0.13} [.328 ^{±.005}]	5/16				277152-3
76.3 ^{±5} GRAMS	9.91 ^{±0.13} [.390 ^{±.005}]	3/8	277152-2			
-	6.73 ^{±0.13} [.265 ^{±.005}]	1/4	[2.81]	[.47]		277152-1
WEIGHT	'A'	'B'	'L'	'C'	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 6/23/89	 TE Connectivity						
DIMENSIONS: MM [INCHES]		CHK MS FEHER 10/16/90							
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD AJ KAUFMAN 10/20/90					
MATERIAL SEE TABLE		FINISH SEE TABLE		PRODUCT SPEC 108-11011		WIRE TERMINAL, RING TONGUE, SEALED COPALUM 71.3mm2 [2/0] ALUMINUM 53.9mm2 [1/0] COPPER			
				APPLICATION SPEC 114-2134		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				WEIGHT SEE TABLE		A2	00779	C=277152	-
		CUSTOMER DRAWING				SCALE	2:1	SHEET	1 of 1
								REV	L