

**BLZP 5.00HC/15/90F SN OR BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Female plugs with clamping-yoke connection for connecting wires with a right-angle (90° or 270°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

**General ordering data**

|              |                                                                                                                                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female plug, 5.00 mm, Number of poles: 15, 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Order No.    | <a href="#">1959340000</a>                                                                                                         |
| Type         | BLZP 5.00HC/15/90F SN OR BX                                                                                                        |
| GTIN (EAN)   | 4032248638222                                                                                                                      |
| Qty.         | 18 pc(s).                                                                                                                          |
| Product data | IEC: 400 V / 23 A / 0.2 - 4 mm²<br>UL: 300 V / 20 A / AWG 26 - AWG 12                                                              |
| Packaging    | Box                                                                                                                                |

**BLZP 5.00HC/15/90F SN OR BX**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 27.1 mm | Depth (inches)  | 1.067 inch |
| Height     | 14.1 mm | Height (inches) | 0.555 inch |
| Width      | 85 mm   | Width (inches)  | 3.346 inch |
| Net weight | 31.94 g |                 |            |

**System Parameters**

|                                              |                                        |                   |              |
|----------------------------------------------|----------------------------------------|-------------------|--------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.00    |                   |              |
| Type of connection                           | Field connection                       |                   |              |
| Wire connection method                       | Clamping yoke connection               |                   |              |
| Pitch in mm (P)                              | 5 mm                                   |                   |              |
| Pitch in inches (P)                          | 0.197 inch                             |                   |              |
| Conductor outlet direction                   | 90°                                    |                   |              |
| Number of poles                              | 15                                     |                   |              |
| L1 in mm                                     | 70 mm                                  |                   |              |
| L1 in inches                                 | 2.758 inch                             |                   |              |
| Number of rows                               | 1                                      |                   |              |
| Pin series quantity                          | 1                                      |                   |              |
| Rated cross-section                          | 4 mm <sup>2</sup>                      |                   |              |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch                 |                   |              |
| Protection degree                            | IP20                                   |                   |              |
| Volume resistance                            | ≤5 mΩ                                  |                   |              |
| Can be coded                                 | Yes                                    |                   |              |
| Stripping length                             | 7 mm                                   |                   |              |
| Clamping screw                               | M 2.5                                  |                   |              |
| Screwdriver blade                            | 0.6 x 3.5, PH 1, PZ 1                  |                   |              |
| Screwdriver blade standard                   | DIN 5264, ISO 8764/2-PH, ISO 8764/2-PZ |                   |              |
| Plugging cycles                              | 25                                     |                   |              |
| Plugging force/pole, max.                    | 10 N                                   |                   |              |
| Pulling force/pole, max.                     | 9 N                                    |                   |              |
| Tightening torque                            | Torque type                            | Wire connection   |              |
|                                              | Usage information                      | Tightening torque | min. 0.4 Nm  |
|                                              |                                        |                   | max. 0.5 Nm  |
|                                              | Torque type                            | Screw flange      |              |
|                                              | Usage information                      | Tightening torque | min. 0.2 Nm  |
|                                              |                                        |                   | max. 0.25 Nm |

**Material data**

|                                       |          |                                       |                                            |
|---------------------------------------|----------|---------------------------------------|--------------------------------------------|
| Insulating material                   | PBT      | Colour                                | orange                                     |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | IIIa                                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Insulation strength                   | ≥ 10 <sup>&lt;sup&gt;8&lt;/sup&gt;</sup> Ω |
| UL 94 flammability rating             | V-0      | Contact material                      | Copper alloy                               |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned                 |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                                     |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                                     |

**Conductors suitable for connection**

|                                         |                      |
|-----------------------------------------|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 4 mm <sup>2</sup>    |
| Wire connection cross section AWG, min. | AWG 30               |

Creation date September 17, 2022 8:03:50 PM CEST

**BLZP 5.00HC/15/90F SN OR BX**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data**

Wire connection cross section AWG, max. AWG 12

Solid, min. H05(07) V-U 0.2 mm<sup>2</sup>Solid, max. H05(07) V-U 4 mm<sup>2</sup>Flexible, min. H05(07) V-K 0.2 mm<sup>2</sup>Flexible, max. H05(07) V-K 4 mm<sup>2</sup>w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm<sup>2</sup> min.w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm<sup>2</sup> max.w. wire end ferrule, DIN 46228 pt 1, 0.2 mm<sup>2</sup> min.w. wire end ferrule, DIN 46228 pt 1, 4 mm<sup>2</sup> max.

Plug gauge in accordance with EN 60999 a x b; ø 2.8 mm x 2.4 mm

Clampable conductor

|                                        |                              |                         |      |
|----------------------------------------|------------------------------|-------------------------|------|
| Cross-section for conductor connection | Type                         | fine-wired              |      |
|                                        | nominal                      | 0.5 mm <sup>2</sup>     |      |
| wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |      |
| Cross-section for conductor connection | Type                         | fine-wired              |      |
|                                        | nominal                      | 1 mm <sup>2</sup>       |      |
| wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |      |
| Cross-section for conductor connection | Type                         | fine-wired              |      |
|                                        | nominal                      | 1.5 mm <sup>2</sup>     |      |
| wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |      |
| Cross-section for conductor connection | Type                         | fine-wired              |      |
|                                        | nominal                      | 2.5 mm <sup>2</sup>     |      |
| wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                                        | Recommended wire-end ferrule | <a href="#">H2.5/7</a>  |      |
| Cross-section for conductor connection | Type                         | fine-wired              |      |
|                                        | nominal                      | 0.75 mm <sup>2</sup>    |      |
| wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |      |

Reference text

The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

**Rated data acc. to IEC**

tested acc. to standard

IEC 60664-1, IEC 61984

Rated current, max. number of poles (Tu=20°C) 18 A

Rated current, max. number of poles (Tu=40°C) 16 A

Rated voltage for surge voltage class / pollution degree III/2 320 V

Rated impulse voltage for surge voltage class/ pollution degree II/2 4 kV

Rated impulse voltage for surge voltage class/ contamination degree III/3 4 kV

Rated current, min. number of poles (Tu=20°C) 23 A

Rated current, min. number of poles (Tu=40°C) 21 A

Rated voltage for surge voltage class / pollution degree II/2 400 V

Rated voltage for surge voltage class / pollution degree III/3 250 V

Rated impulse voltage for surge voltage class/ pollution degree III/2 4 kV

Short-time withstand current resistance 3 x 1s with 120 A

## BLZP 5.00HC/15/90F SN OR BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

www.weidmueller.com

200039-1121690

Rated voltage (Use group B / CSA) 300 V

Rated voltage (Use group C / CSA) 50 V

Rated voltage (Use group D / CSA) 300 V

Rated current (Use group B / CSA) 20 A

Rated current (Use group D / CSA) 20 A

Wire cross-section, AWG, min. AWG 30

Wire cross-section, AWG, max.

Reference to approval values

Specifications are maximum values, details - see approval certificate.

AWG 12

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 27 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |

## Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional variants on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cULus) | E60693     |

Creation date September 17, 2022 8:03:50 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

**BLZP 5.00HC/15/90F SN OR BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

**Technical data**[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Downloads**

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Product Change Notification                 | <a href="#">20220106 BLT and BLZP in pitch 5.0x – Addition of a screw locking</a><br><a href="#">20220106 BLT und BLZP im Raster 5.0x – Ergänzung einer Schraubensicherung</a>                                                                                                                                                                                                                                                                                                                                                                                                     |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


**BLZP 5.00HC/15/90F SN OR BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold





Tel. +49 5231 14-0

Fax. +49 5231 14-2083





**Drawings****Dimensional drawing** [info@weidmueller.com](mailto:info@weidmueller.com)

MIN. FRONT PLATE CUT-OUT

BLZP 5.00HC/04/270F



BLZP 5.00HC/04/90F



For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

P = 5.00 RASTER/PITCH

n = POLZAHL/NO OF POLES

SHOWN: BLZP 5.00HC/04/90F  
BLZP 5.00HC/04/270F

|    |         |           |
|----|---------|-----------|
| 24 | 115,00  | 4,53      |
| 23 | 110,00  | 4,33      |
| 22 | 105,00  | 4,13      |
| 21 | 100,00  | 3,94      |
| 20 | 95,00   | 3,74      |
| 19 | 90,00   | 3,54      |
| 18 | 85,00   | 3,35      |
| 17 | 80,00   | 3,15      |
| 16 | 75,00   | 2,95      |
| 15 | 70,00   | 2,76      |
| 14 | 65,00   | 2,56      |
| 13 | 60,00   | 2,36      |
| 12 | 55,00   | 2,17      |
| 11 | 50,00   | 1,97      |
| 10 | 45,00   | 1,77      |
| 9  | 40,00   | 1,57      |
| 8  | 35,00   | 1,38      |
| 7  | 30,00   | 1,18      |
| 6  | 25,00   | 0,98      |
| 5  | 20,00   | 0,79      |
| 4  | 15,00   | 0,59      |
| 3  | 10,00   | 0,39      |
| 2  | 5,00    | 0,20      |
| n  | L1 [mm] | L1 [inch] |

GENERAL TOLERANCE:  
DIN ISO 2768-m



99339/0  
19.02.18 HERTEL\_S 01

Modification

**Weidmüller**



Cat.no.: .

**3 42481**

**06**

Drawing no. Issue no.  
Sheet 02 of 04 sheets



Scale: 2:1

Supersedes: .

| Date        | Name     |
|-------------|----------|
| Drawn       | HERTEL_S |
| Responsible | HERTEL_S |
| Checked     | HELIS_MA |
| Approved    | LANG_T   |

**BLZP 5.00HC/./90/270**  
BUCHSENLEISTE  
SOCKET BLOCK

Product file: BLZP 5.0X WG

7157