

REV. 0
DCO 143680


COIL: @ 25°C	
RESISTANCE	1130 OHMS ±10%
NOMINAL VOLTAGE	18.0 VDC
MUST OPERATE	10.7 VDC
TURN-ON BASE CURRENT	0.21 mADC
MUST RELEASE	6.0 VDC MAX, 0.94 VDC MIN.

ENVIRONMENT:

VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: TURN-ON TIME 2.0 MS MAX.
TURN-OFF TIME 4.0 MS MAX.
CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 31 OCT 02 CK 10/31/02

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M28776/5-029P REV.

"J1MAT" RELAY

J1MACT-18XP