





COIL: @ 25°C  
 RESISTANCE 1560 OHMS ± 10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 15.2 VDC  
 MUST RELEASE 9.5 VDC MAX, 1.8 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX  
 RELEASE TIME 4 MS MAX  
 CONTACT STABILIZATION 2.0 MS MAX

# CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 6/10/97 CK *[Signature]* 6/10/97

**COMMUNICATIONS  
 INSTRUMENTS, INC.**

CUST. QPL  
 CUST. NO. M39016/20-012M

TYPE "JMADD" RELAY

**JMAWDD-26XM**