




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REDRAWN PER EC 0020-774-94	09/15/94	-	AF
E		REVISED PER ECO-17-016115	02NOV2017	RS	MZ

- 1 THIS CONNECTOR ACCEPTS FIVE (5) SIZE 16 MULTIMATE SOCKET CONTACTS.
MAXIMUM WIRE INSULATION DIAMETER = $\phi .135$
- 2 THIS CONNECTOR MATES WITH AMP P/N 208720-1.
- 3 PART NUMBER AND DATE CODE MARKED ON ANY ANY FLANGE EDGE.
- 4 THERMOPLASTIC, BLACK.
- 5 ZINC PER QQ-Z-363.
- 6 NICKEL PER QQ-N-290 OVER COPPER PER MIL-C-14550.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

SOCKET HOUSING: 4
RECEPTACLE SHELL: 6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.13[.005]
3 PLC	±	-
ANGLES	±	-
FINISH		

RECEPTACLE SHELL: 6

DWN
T. SMITH
3/19/82

CHK
B. LENKER
9/26/94

APVD
A. FRANTUM
9/29/94

PRODUCT SPEC
108-10040

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
RECEPTACLE ASSEMBLY, REVERSE SEX,
SERIES I, 14-5, CMC
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=208721

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
E