






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-14-005775	21APR2014	AP	DD

1.6 MIN
BOARD THICKNESS

1.2
TAIL LENGTH




- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
- 4 UNGUIDED RIGHT ANGLE MALE MATES TO
UNGUIDED RIGHT ANGLE RECEPTACLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	06APR2011		 TE Connectivity						
DIMENSIONS:		CHK	06APR2011								
mm			J. EABY		NAME	IMPACT, STD, RAM, 2 PAIR, 10 COLUMN, UNGUIDED OPEN END WALL SIGNAL MODULE, 0.39 EYELET					
			APVD								
			J. EABY								
			PRODUCT SPEC								
			-								
	ANGLES		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
			-								
			-								
			-								
			-								
MATERIAL			WEIGHT		A100779	C=2143012	-	REV			
			-								
			-								
			-								
			-								
SEE TABLE		CUSTOMER DRAWING		SCALE		5:1		SHEET 1 OF 2		REV B	

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-



COPLANAR MATED SIGNAL PATHS



	5.50	2143012-6
	4.90	2143012-5
	5.50	2143012-3
	4.90	2143012-2
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	06APR2011	TE Connectivity	
		CHK	06APR2011		
		J. EABY		NAME	
		APVD	06APR2011		
		J. EABY		PRODUCT SPEC	
				APPLICATION SPEC	
				SIZE	
				CAGE CODE	
				DRAWING NO.	
				RESTRICTED TO	
				REV	
				B	