






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	26AUG2019	AY	PS
	A1	REMOVED TOLERANCE FROM DIM F	17DEC2019	AY	PS

- NOTES:
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.1 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: BULK PACK.
 - TOLERANCE NOT CUMULATIVE.
 - CUTTING BURR MAX. 0.25 mm.




RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW / PIN-IN-PASTE

1-2355172-0 AS SHOWN



48.0	50.0	25	2-2355172-5
46.0	48.0	24	2-2355172-4
44.0	46.0	23	2-2355172-3
42.0	44.0	22	2-2355172-2
40.0	42.0	21	2-2355172-1
38.0	40.0	20	2-2355172-0
36.0	38.0	19	1-2355172-9
34.0	36.0	18	1-2355172-8
32.0	34.0	17	1-2355172-7
30.0	32.0	16	1-2355172-6
28.0	30.0	15	1-2355172-5
26.0	28.0	14	1-2355172-4
24.0	26.0	13	1-2355172-3
22.0	24.0	12	1-2355172-2
20.0	22.0	11	1-2355172-1
18.0	20.0	10	1-2355172-0
16.0	18.0	9	2355172-9
14.0	16.0	8	2355172-8
12.0	14.0	7	2355172-7
10.0	12.0	6	2355172-6
8.0	10.0	5	2355172-5
6.0	8.0	4	2355172-4
4.0	6.0	3	2355172-3
2.0	4.0	2	2355172-2
DIM "F"	DIM "E"	POS	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09APR2019 RAGHAVENDRA K	 TE Connectivity	
DIMENSIONS: mm		CHK 14AUG2019 KARTHIK.JK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 16AUG2019 PRASHANTH	NAME AMPMODU 2mm BREAKAWAY HEADER SINGLE ROW, VERTICAL, 0.1 Au, BULK	
0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-64040	SIZE A2	
ANGLES ±2°		APPLICATION SPEC 114-32259	CAGE CODE 00779	
FINISH		WEIGHT -	DRAWING NO C-2355172	
MATERIAL SEE NOTES		CUSTOMER DRAWING		RESTRICTED TO -
-		SCALE 10:1		REV A1

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.