







| SWITCH FUNCTION |        |          |
|-----------------|--------|----------|
| POS. 1          | POS. 2 | POS. 3   |
|                 |        |          |
| ON              | NONE   | ON       |
| 2-3, 5-6        | N/A    | 2-1, 5-4 |



## NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A @ 250 VAC  
5A @ 120 VAC OR 28 VDC
- ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
- DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
- OPERATING TEMP.: -40°C TO 85°C
- ▲ DENOTES CRITICAL PARAMETER.

| REV | ECO NO     | DESCRIPTION       | DATE     | BY | E-SWITCH®             |          |     |         | OBJECT ID |
|-----|------------|-------------------|----------|----|-----------------------|----------|-----|---------|-----------|
| B   | ECO-102490 | 100 SERIES UPDATE | 02/21/24 | MR | TITLE 100DP1T2B1M71QE |          |     |         | 000023921 |
|     |            |                   |          |    | SCALE                 | DATE     | DR  | DWG     | REV       |
|     |            |                   |          |    | 2:1                   | 1/9/2013 | EBP | T111120 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED