



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50						
			G	REVISED PER ECR-08-008189	24NOV08	HMR	DD




- 1 CONTINUOUS STRIP ON REELS
- 2 TIN PLATING.
- 3 PARTS TO BE REELED WITH INTERLEAVE PAPER.



METRIC

F	4.57 [.180]	6.35 [.250]	F	2.54 [.100]	2.11 [.083]	1.3mm ² [16]
					1.96 [.077]	0.8mm ² [18]
					1.85 [.073]	0.5mm ² [20]
					1.80 [.071]	0.3mm ² [22]
TYPE	WIDTH	STRIP LENGTH ±0.38 [±.015]	TYPE	WIDTH	HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

2		2.54—3.56 [.100—.140]		0.3mm ² —1.3mm ² [22—16] AWG		61436—2	
—						61436—1	
FINISH		INSULATION RANGE		WIRE SIZE		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 3/1/90		 Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105—3608			
		CHK JR RUTH 3/2/90					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD G YETTER 3/5/90		RING			
		PRODUCT SPEC					
		—					
		APPLICATION SPEC					
		—		SIZE		CAGE CODE	
		—		DRAWING NO		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		—	
#4 HARD BRASS		SEE TABLE		—			
CUSTOMER DRAWING				SCALE		SHEET	
				5:1		1 OF 1	
						REV	
						G	