

SPECIFICATIONS:

MATERIALS:

BACKSHELL:	DIE CAST NICKEL PLATED ZINC ALLOY
JACKSCREWS:	ZINC PLATED STEEL
HOOD SCREWS:	ZINC PLATED STEEL
COMPRESSION INSERTS:	ABS, UL 94-HB


ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +120°C

BACKSHELL KIT INCLUDES:
 (2) BACKSHELL HALVES
 (2) 4-40 THUMBSCREWS
 (2) HOUSING SCREWS (RECOMMENDED TORQUE 5.2 IN-LBS)
 (1) COMPRESSION INSERTS - VARIOUS SIZES
 $\varnothing 0.157$ [4.0], $\varnothing 0.197$ [5.0], $\varnothing 0.276$ [7.0], $\varnothing 0.354$ [9.0]

NOTE: 9 POSITION HAS ONLY 1 THUMBSCREW (OPPOSITE CABLE ENTRY)

DIMENSIONS(in/mm)				
SIZE	A	B	C	D
9	1.220	0.984	1.429	0.570
	30.99	24.99	36.30	14.48
15	1.556	1.312	1.587	0.570
	39.50	33.32	40.30	14.48
25	2.094	1.852	1.587	0.570
	53.20	47.04	40.30	14.48
37	2.744	2.500	1.587	0.570
	69.70	63.50	40.30	14.48



971-YYY-030R121
 SERIES _____
 POSITIONS _____
 009
 015
 025
 037
 MATERIAL _____
 030 = ZINC
 COLOR: _____
 12 = NICKEL OVER COPPER
 PUT-UPS _____
 1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
 THE PROPERTY OF NorComp AND SHALL NOT
 BE REPRODUCED, COPIED OR USED AS THE
 BASIS FOR THE MANUFACTURE OR SALE OF
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
 P. JENKINS
 DATE:
 06/10/2005

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 10
DWG NO. 971-YYY-030R121		