








NOTES:

1. MATERIALS:
HOUSING: PA 6/6
CONTACT RETAINER: STAINLESS STEEL
GROMMET: SILICONE RUBBER PER A-A-59588
2. OPERATING RANGE:
TEMPERATURE: -55 °C TO 95 °C
INSULATION RESISTANCE: 5000 MEGOHMS MINIMUM
DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS SEA LEVEL
600 VRMS @ 45,000 FT. ALTITUDE
- CURRENT RATING: 7.5 AMPS
VIBRATION: PER EIA-364D METHOD 28, TEST CONDITION V.
3. ACCEPTS (3) M39029/56-351 SOCKET CONTACT (NOT INCLUDED)
4. CONTACT RETENTION - 20 LBS EACH

REV	ECN	APP'D
-	5663	J. TON
A	5706	J. TON
B	5796	J. TON
C	5951	J. TON
D	6102	J. TON
E	6589	<i>J. T. 12/10</i>



PART MARKING AS FOLLOWS:
BACC63DE0320SX APCD
YYWW SJS6201XX
DATE CODE
SEE TABLE 1 FOR FULL PART NUMBERS

KEY CONFIGURATION SEE TABLE 1

TABLE 1 - PART NUMBER SCHEME			
APCD PART#	BACC PART#	KEY	COLOR
SJS620100	BACC63DE0320SA	A	RED
SJS620110	BACC63DE0320SB	B	WHITE
SJS620120	BACC63DE0320SC	C	BLUE

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE		TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±1.0°		PROJECTION 		Amphenol Pcd SPECIFICATION DRAWING ENGR S. STONE 10/19/05		TITLE IN-LINE JUNCTION TRIPLE WIRE, SIZE 20 PLUG						
ORIGINAL 		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA				CHKD  10/12/10 APPD  12/12/10		SIZE B		DWG NO. SJS620100			REV E	
						CODE: 58982		SCALE: 2:1		SHEET 1 OF 1				