


12		11		10		9		8		7		6		5		4		3		2		1	
MATERIAL NUMBER LOOSE PCS	ENGINEERING NUMBER LOOSE PCS	MATERIAL NUMBER ON STRIP	ENGINEERING NUMBER ON STRIP	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	MATERIAL NUMBER REVERSE WOUND		ENGINEERING NUMBER REVERSE WOUND		ACCEPTS TAB SIZE		STOCK THICKNESS		"A" MAX	"B" MAX	"F" REF	"G" MAX	"H" REF					
190020024	BB-5263	190020027	BB-5263Z	190020025	BB-5263T	190020026		BB-5263TR		.250x.032 (6.35x0.81)		.016/0.41		.89/22.6	.38/9.7	.16/4.1	.20/5.1	1.425/36.20					
190020040	BB-5287	190020041	BB-5287Z	190020048	BB-5287T	---		---		.205x.020 (5.21x0.51)		.016/0.41		.80/20.3	.32/8.1	.16/4.1	.22/5.6	1.415/35.94					
190020042	BB-5289	190020061	BB-5289Z	190020043	BB-5289T	---		---		.205x.032 (5.21x0.81)		.016/0.41		.80/20.3	.32/8.1	.16/4.1	.22/5.6	1.415/35.94					
190020028	BB-5269	190020030	BB-5269Z	190020029	BB-5269T	---		---		.187x.020 (4.75x0.51)		.016/0.41		.80/20.3	.32/8.1	.16/4.1	.22/5.6	1.415/35.94					
190020031	BB-5273	190020033	BB-5273Z	190020032	BB-5273T	---		---		.187x.032 (4.75x0.81)		.016/0.41		.80/20.3	.32/8.1	.16/4.1	.22/5.6	1.415/35.94					
190020034	BB-5277	190020036	BB-5277Z	190020035	BB-5277T	---		---		.110x.020 (2.79x0.51)		.012/0.31		.80/20.3	.23/5.8	.13/3.3	.22/5.6	1.395/35.43					
190020037	BB-5281	190020039	BB-5281Z	190020038	BB-5281T	---		---		.110x.032 (2.79x0.81)		.012/0.31		.80/20.3	.23/5.8	.13/3.3	.22/5.6	1.395/35.43					



- NOTES:
- MATERIAL: TERMINAL BRASS
TERMINAL PLATING: ELECTRO TIN
FERRULE: COPPER ALLOY
FERRULE PLATING: ELECTRO TIN
INSULATION: NYLON 94V2, COLOR BLUE.
 - MWID = MAXIMUM WIRE INSULATION DIAMETER
 - ASSEMBLY IS RoHS COMPLIANT.

DOCUMENT STATUS	P1	RELEASE DATE	2019/01/03 19:35:51
-----------------	----	--------------	---------------------

12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	---	---	---	---	---	---	---	---	---

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADD MAX CUTOFF				molex AVIKRIMP FEMALE FIQD 16-14 AWG			
 = 0	IN/MM		1:1									
 = 0												
GENERAL TOLERANCES (UNLESS SPECIFIED)					EC NO: 609893 DRWN: DMYRICK 2019/01/02 CHK'D: JMACNEIL 2019/01/03 APPR: JMACNEIL 2019/01/03				PRODUCT CUSTOMER DRAWING			
 = 0		MM	INCH									
 = 0	4 PLACES	±	±									
 = 0	3 PLACES	±	± 0.005									
 = 0	2 PLACES	± 0.13	± 0.01									
 = 0	1 PLACE	± 0.25	±	INITIAL REVISION: DRWN: BENDERLE 2005/04/25 APPR: RDEROSS 2005/04/26				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
 = 0	0 PLACES	±	±					SD-19002-004		PSD	001	F2
 = 0	ANGULAR TOL ± 0.5 °											
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
						C-SIZE	19002	SEE CHART		GENERAL MARKET		1 OF 1

AVIKRIMP FEMALE FIQD
16-14 AWG

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SD-19002-004

DOC TYPE

PSD

DOC PART

001

REVISION

F2