



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE GOLD PLATED VERSIONS TO PRODUCTION	03SEP2019	AY	PS
	A1	RELEASE TIN PLATED VERSIONS TO PRODUCTION	14APR2020	AY	PS




1. MATERIAL:
HOUSING & CAP: LCP, UL94 V0, BLACK
CONTACT: PHOSPHOR BRONZE, 0.20mm THICK,
2. ALL OVER 3-5 μ m TIN OVER MIN 1.27 μ m NICKEL UNDERPLATE
3. CONTACT AREA: MIN 0.1 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER
4. CONTACT AREA: MIN 0.38 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER
5. CONTACT AREA: MIN 0.76 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER
6. N = NO. OF POSITIONS PER CONNECTOR.


P&P CAP	3
CONTACT	2
HOUSING	1
DESCRIPTION	ITEM




RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE




RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW / PIN-IN PASTE



2307764-2



2307764-8



1-2307764-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29AUG2017 CHK SOURAV DAS 17JULY2018 APVD SHARATH S 17JULY2018		 TE Connectivity	
DIMENSIONS: mm [inch]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMPMODU 2mm BtB RECEPTACLE SINGLE ROW VERTICAL.TOP ENTRY TH/THR -	
		0 PLC ±- 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±- [0.004] 4 PLC ±- ANGLES ±2° FINISH			
MATERIAL SEE NOTES -		SEE NOTES -		PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32186 WEIGHT - CUSTOMER DRAWING	
				SIZE A2	CAGE CODE 00779
				DRAWING NO C=2307764	
				RESTRICTED TO -	
				SCALE 5:1	SHEET 1 OF 2
				REV A1	

