







PCB LAYOUT
Bottom view



Dimension

DIM A	$(N-1) \times 7.62 + 5.98$
DIM B	$(N-1) \times 7.62$

N=Number of poles

POLES	DIM B	DIM A
2p-4p	± 0.15	± 0.20
5p-8p	± 0.20	± 0.25
9p-12p	± 0.25	± 0.30
13p-16p	± 0.30	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/27'07	The soldering temperature from 245°to 250°	Aaron
△	10/09'12	Update the drawing	Da cheng
△	04/11'13	Update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Terminal body (Contact pin): Brass, Tin plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Pull force:
- Screw:
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 
- Critical dimension: 

HG xx 50 x 0 xxxx G

02 2 CONTACTS	Color △△	000 0 Standard @ Logo	RoHS compliant
03 3 CONTACTS	0 Black (RAL9005)	000 A Standard ANY Logo	(lead<4%) △
...	2 Red (RAL3001/D)	Any special item by	In copper Alloy
...	3 Orange(RAL2011/P)	customer request,	
16 16 CONTACTS	4 Yellow(RAL1018/A)	please contact sales	
	5 Green(RAL6018/T)	department.	
	6 Blue (RAL5015/A)		
	8 Grey(RAL7004/P)		
	9 White(RAL1102)		
	C Multiple colors		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HG 7.62mm Series						
PART NO.		HGxx50x0xxxxG			DWG NO.	8HG0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Da cheng 2013.04.11	Da cheng 2013.04.11		UNIT: mm		X. ±0.50	
					SCALE: NONE		X.X ±0.30	
					SHEET: 01/01		X.XX ±0.10	
					REV.: F		X° ±1°	