









General tolerances(mm)														0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2°



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
UL Standard		B	C	D
Rated Voltage(V)/Current(A)		150/6	/	/
IEC Standard				
Overvoltage Category/Pollution Degree		III/3	III/2	III/2
Rated Voltage(V)/Current(A)		/	130/8	/
Withstanding Voltage(V/1min)		/	AC2000	/
Torque Tightening(N·m/Lb.in)		M1.6, 0.15/1.3		
Wire Range(rigid and flexible)(mm²/AWG)		26~18/0.5~1.0		
Pitch(mm)/Poles		2.54/N=02~18P		
Stripping length(mm)		5~6		
Operating temperature(°C)		-40~+105		
Conform to RoHS		Yes		

PCB LAYOUT



4	Screw	Steel	M1.6/Zn Plated
3	Cage	Copper Alloy	M1.6/Ni plated
2	Housing	PA66	UL94V-0
1	Pin header	Copper alloy	Sn Plated
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
		PART NO.	TITLE:	
		C254128V-NPOG36	Socket-type terminal	
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		SCALE
FINISH	— — —	APPD: Ava		SHEET
			N:A	1/1