

High IP3 Frequency Mixer

Level 17 (LO Power +17 dBm) 20 to 750 MHz

ADE-751H+



Generic photo used for illustration purposes only

CASE STYLE: CD541


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	4
IF	3
GROUND	1,2,5

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch)

A	B	C	D	E	F	G
.272	.310	.220	.100	.082	.055	.100
6.91	7.87	5.59	2.54	2.08	1.40	2.54
H	J	K	L			wt
.030	.026	.065	.300			grams
0.76	0.66	1.65	7.62			0.15

Demo Board MCL P/N: TB-02+ Suggested PCB Layout (PL-051)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- high IP3, 27 dBm typ.
- low conversion loss, 6.5 dB typ.
- good L-R isolation, 42 dB typ.
- low profile package
- aqueous washable
- protected by U.S. Patent 6,133,525

Applications

- cellular


Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Frequency Range, RF	20	—	750	MHz
Frequency Range, LO	50	—	780	MHz
Frequency Range, IF	DC	—	250	MHz
Conversion Loss	—	6.5	8.0	dB
LO to RF Isolation	28	42	—	dB
LO to IF Isolation	27	40	—	dB
IP3	—	27	—	dBm
RF Input Power at 1 dB Compression	—	+9	—	dBm

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)	IP3 (dBm)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
20.10	50.10	6.55	62.00	64.65	1.24	2.86	28.64
50.10	80.10	6.51	57.54	61.04	1.22	2.96	40.05
100.10	130.10	6.51	53.50	58.09	1.21	2.77	38.21
150.10	180.10	6.50	50.42	54.59	1.21	2.83	32.38
200.10	230.10	6.45	48.87	52.36	1.21	2.67	30.83
250.10	280.10	6.37	47.00	49.43	1.20	2.81	30.69
300.10	330.10	6.30	46.10	48.17	1.20	2.69	29.85
350.10	380.10	6.31	44.73	45.32	1.19	2.81	28.17
400.10	430.10	6.21	44.09	45.53	1.19	2.68	27.83
450.10	480.10	6.14	43.50	42.41	1.18	2.83	28.33
500.10	530.10	6.20	42.96	42.40	1.21	2.70	34.04
550.10	580.10	6.05	42.26	41.46	1.16	2.78	27.56
600.10	630.10	6.06	42.54	39.50	1.14	2.76	24.27
650.10	680.10	6.11	42.37	37.81	1.14	2.98	27.81
700.10	730.10	6.18	42.01	37.68	1.14	2.93	29.20
710.10	740.10	6.14	41.83	37.47	1.12	2.96	28.44
720.10	750.10	6.12	41.70	37.39	1.11	2.97	27.37
730.10	760.10	6.14	41.50	37.25	1.11	2.97	26.07
740.10	770.10	6.13	41.19	37.16	1.11	2.99	25.24
750.10	780.10	6.10	40.97	37.19	1.10	2.97	24.34








Electrical Schematic



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ADE-751H+
ED-14942/1
DJ/CP/AM
200420
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

