







3 PIN




4 PIN



5 PIN



6 PIN



7 PIN

STANDARD SERIES


SCREW - STAINLESS STEEL
SHELL - STAINLESS STEEL
LATCH BUTTON - ZINC, NICKEL PLATED
INSULATOR - POLYESTER, GREEN
SOLDER TERMINAL - BRASS, ELECTRO TIN
LATCH SPRING - STAINLESS STEEL
CONTACT PIN - PHOSPHOR BRONZE, SILVER PLATED
HOUSING - ZINC
RELEASE LEVER - STEEL, NICKEL PLATED

- CONTACT PLATING:
BLANK = SILVER (STANDARD)
AU = GOLD
- HOUSING FINISH:
BLANK = TEXTURED (STANDARD)
S = SANDED
- HOUSING PLATING: SEE NOTE 2
BLANK = NICKEL PLATE (STANDARD)
BX = BLACK RoHS
- LATCH TYPE:
BLANK = STANDARD LATCHLOCK
D = FAS-DIS-CONNECT DETENT (SEE FIGURE 1)
(NO LATCH)
- NO. OF CONTACTS:
3 = 3 CONTACTS
4 = 4 CONTACTS
5 = 5 CONTACTS
6 = 6 CONTACTS
7 = 7 CONTACTS


PROFESSIONAL SERIES

HOUSING FINISH - MATTE CHROME
CONTACT PLATING - GOLD

- OGP 62
- NO. OF CONTACTS:
3 = 3 CONTACTS




RECOMMENDED
PANEL CUT-OUT




NOTES:

1. ALL DIMENSIONS REF. UNLESS OTHERWISE SPECIFIED.
2. BLACK HOUSING AND INSERT WITH SATIN NICKEL PLATED LATCH.
3. THIS PRODUCT IS RoHS COMPLIANT.



FRONT VIEW



SIDE VIEW

FIGURE 1
3 PIN DETENT VERSION
(NO LATCH)

CUSTOMER DRAWING

						★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - FRACTIONAL DIMENSIONS ±1/64 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTER LINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY. <table><tr><td>SIZE</td><td>WIDTH</td><td>MULT</td><td>LBS/M</td><td>TEMPER</td></tr><tr><td colspan="5">FINISH</td></tr><tr><td colspan="3">SPEC No.</td><td colspan="2">MATERIAL SPEC No.</td></tr><tr><td colspan="2">FIRST USED ON</td><td colspan="3">SCALE 2:1</td></tr><tr><td>DATE DRAWN</td><td>BY</td><td>CHKD</td><td colspan="2">APVD</td></tr><tr><td>7-Feb-94</td><td>SG</td><td>AA 7-11-94</td><td colspan="2">GHJ 7-11-94</td></tr><tr><td colspan="5">NAME</td></tr><tr><td colspan="5">D SERIES FEMALE OG, RoHS</td></tr></table> Switchcraft® <table><tr><td>SHEET</td><td>1</td><td>OF</td><td>1</td></tr><tr><td colspan="2">PART No.</td><td colspan="2">REV</td></tr><tr><td colspan="2">D F SERIES</td><td colspan="2">S</td></tr></table>	SIZE	WIDTH	MULT	LBS/M	TEMPER	FINISH					SPEC No.			MATERIAL SPEC No.		FIRST USED ON		SCALE 2:1			DATE DRAWN	BY	CHKD	APVD		7-Feb-94	SG	AA 7-11-94	GHJ 7-11-94		NAME					D SERIES FEMALE OG, RoHS					SHEET	1	OF	1	PART No.		REV		D F SERIES		S	
SIZE	WIDTH	MULT	LBS/M	TEMPER																																																							
FINISH																																																											
SPEC No.			MATERIAL SPEC No.																																																								
FIRST USED ON		SCALE 2:1																																																									
DATE DRAWN	BY	CHKD	APVD																																																								
7-Feb-94	SG	AA 7-11-94	GHJ 7-11-94																																																								
NAME																																																											
D SERIES FEMALE OG, RoHS																																																											
SHEET	1	OF	1																																																								
PART No.		REV																																																									
D F SERIES		S																																																									
S	26158	10-4-06	TO	TJK																																																							
R	ECO #22895	9-20-99	TJK	TJK																																																							
REV	ECO NUMBER	DATE	BY	APVD																																																							
REVISIONS																																																											