






General tolerances(mm)														0.1/10 ±2°
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN	
UL Standard			B	C	D
Rated Voltage(V)/Current(A)			300/10	/	/
IEC Standard					
Overvoltage Category/Pollution Degree			Ⅲ/2		
Rated Voltage(V)/Current(A)			250/18		
Withstanding voltage(V/1Min)			AC2000		
Torque Tightening(N-m/Lb.in)			M2.6,0.34~0.4/3.1~3.6		
Wire Range(rigid and flexible)(mm²/AWG)			26~14/0.5~2.5		
Pitch(mm)/Poles			5.00/N=02~24P		
Stripping length(mm)			6mm~7mm		
Operating temperature(°C)			-40°~+105°		
Conform to RoHS			Yes		



PCB LAYOUT

4	Pin Header	Iron	Sn Plated
3	Spring	Stainless steel	/
2	Screw	Steel	M2.6/Zn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
		PART NO.	TITLE:		
		C50126V-NP0G56	Socket-type terminal		
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	---	CHED: Olvia		SCALE	SHEET
FINISH	---	APPD: Ava		N:A	1/1