

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

2129691-2 AS SHOWN

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-19-002924	14MAR2019	R.Z	S.L

NOTES:

△ MATERIAL:

- ① SHELL: STAINLESS STEEL
- ② SHELL BRACKET: STAINLESS STEEL
- ③ HOUSING: HIGH TEMPERATURE THERMO PLASTIC ,BLACK, UL94V-0
- ④ UPPER CONTACT: COPPER ALLOY
- ⑤ LOWER CONTACT: COPPER ALLOY
- ⑥ MID-PLATE: STAINLESS STEEL

△ FINISH:

CONTACT: ALL OVER NI PLATING<2.0UM
CONTACT AREA AU PLATING<0.75UM
SOLDER AREA TIN PLATING<2.0UM
SHELL: ALL OVER NI PLATING<1.3UM
BRACKET: ALL OVER NI PLATING<1.3UM
MID-PLATE: ALL OVER NI PLATING<1.3UM.

△ TE LOGO




△ DATE CODE

YYWWDD**

ASSY LINE NO: A,B,C,***

△ VACUUM AREA

DAY SHIFT OR NIGHT SHIFT



PIN NO.	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
SIGNAL NAME	GND	SSTxp1	SSTxm1	VBUS	CC1	Dp1	Dn1	SBUL	VBUS	SSRx2	SSRx2	GND
PIN NO.	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
SIGNAL NAME	GND	SSRxp1	SSRxm1	VBUS	SBUL	Dn2	Dp2	CC2	VBUS	SSTxm2	SSTxp2	GND


2129691-2

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.15
4 PLC	± -
ANGLES	± 3°

FINISH

SEE NOTE

DWN 26APR2018

CHK T.ZHU 26APR2018

S.LI 26APR2018

APVD S.LI 26APR2018

PRODUCT SPEC

108-99061

APPLICATION SPEC

—

WEIGHT —

CUSTOMER DRAWING



TE Connectivity

TYPE-C RECTACLAEE ASSEMBLY
OFFSET 0.485MM HYBRID TYPE

SIZE

A3

CAGE CODE

C=2129691

DRAWING NO

—

RESTRICTED TO

—

SCALE

—

SHEET

1 OF 4

REV

B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


- . - .

© COPYRIGHT - TE Connectivity Ltd.


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



(GROUND PINSOLDERABLE WIDTH)



Coplanarity 0.08 Max(B.R)

Coplanarity 0.10 Max(A.R)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T.ZHU 26APR2018

CHK S.LI 26APR2018

APVD S.LI 26APR2018

PRODUCT SPEC
108-99061

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING



TE Connectivity

TYPE-C RECPTACLAEE ASSEMBLY
OFFSET 0.485MM HYBRID TYPE

SIZE A3


CAGE CODE

DRAWING NO

C=2129691

RESTRICTED TO

REV B1

DIMENSIONS:
mmMATERIAL
SEE NOTETOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± 0.25
2 PLC ± 0.15
3 PLC ± 0.10
4 PLC ± -
ANGLES ± 3°

SEE NOTE

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

NOTES:

1.P/N:P-ZA-172309

2.USED ON USB TYPE C RECEPTOR CONNECTOR PRODUCTS.





3.PACKAGE:1000PCS/REEL,10REELS/BOX

4.MATERIAL:TRANSPARENT CONDUCTIVE POLYSTYRENE ALLOY

5.APPLICABLE DOCUMENTS:IEA-481-D

6.AFTER UNREELING DIRECTION MUST HAVE 11PCS BLANK.(170mm Min)

7.BEFORE UNREELING DIRECTION MUST HAVE 25PCS BLANK.(400mm Min)



PACKAGING PROCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T.ZHU 26APR2018

CHK S.LI 26APR2018


APVD S.LI 26APR2018

PRODUCT SPEC
108-99061

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:
mm

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.15
4 PLC	± -
ANGLES	± 3°

SEE NOTE



TE Connectivity

TYPE-C RECEPTACLE ASSEMBLY
OFFSET 0.485MM HYBRID TYPE

SIZE

A3

CAGE CODE

DRAWING NO

C=2129691

RESTRICTED TO

-

SCALE -

SHEET

4 OF 4

REV

B1

2129691-2

PART NUMBER