






PANEL CUTOUT
MAX. PANEL THICKNESS
10.0mm [.43]



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
(ON)	ON	(ON)
1-3, 4-5	1-3, 4-6	1-2, 4-6
() DENOTES MOMENTARY		



- NOTE:
1. ALL DIMENSIONS IN mm [INCH]
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT MATERIAL: SILVER
 5. RATING: 2A 24VDC
 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
 7. INSULATION RESISTANCE: 1,000 MΩ MIN.
 8. DIELECTRIC STRENGTH: 1,500 VAC MIN. FOR 1 MINUTE
 9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
 10. OPERATING TEMP.: -20°C to 55°C
 11. ▲ DENOTES CRITICAL PARAMETER.
 12. INGRESS PROTECTION: IP40
 13. HARDWARE SUPPLIED: O-RING AND HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
B	ECO-102081	ACTUATOR DIMS CHANGE TO REFERENCE	07/13/23	JS				100122493
					TITLE PVK4S22D0SS			
					SCALE 1:1 DATE 7/26/2022 DR MJR DWG 52-PVK4S22D0SS			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					REV			B