IXYS

PolarHT™ Power MOSFET

IXTQ 140N10P
IXTT 140N10P

V_{DSS} = 100 V
I_{D25} = 140 A
$R_{DS(on)}$ ≤ 11 mΩ

N-Channel Enhancement Mode
Avalanche Rated



Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25° C to 175° C	100	V
V_{DGR}	T_J = 25° C to 175° C; R_{GS} = 1 MΩ	100	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25° C	140	A
$I_{D(RMS)}$	External lead current limit	75	A
I_{DM}	T_C = 25° C, pulse width limited by T_{JM}	300	A
I_{AR}	T_C = 25° C	60	A
E_{AR}	T_C = 25° C	80	mJ
E_{AS}	T_C = 25° C	2.5	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤100 A/μs, $V_{DD} \le V_{DSS}$, T_J ≤150° C, R_G = 4 Ω	10	V/ns
P_D	T_C = 25° C	600	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
T_{SOLD}	Plastic body for 10 s	260	°C
M_d	Mounting torque (TO-3P)	1.13/10	Nm/lb.in.
Weight	TO-3P	5.5	g
	TO-268	5.0	g

TO-3P (IXTQ)



TO-268 (IXTT)



G = Gate D = Drain
S = Source TAB = Drain

Features

- International standard packages
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect

Advantages

- Easy to mount
- Space savings
- High power density

Symbol	Test Conditions (T_J = 25° C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 μA	100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 250μA	3.0		5.0	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$			25	μA
	V_{GS} = 0 V T_J = 175° C			500	μA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5\ I_{D25}$			11	mΩ
	V_{GS} = 15 V, I_D = 300 A		9		mΩ
	Pulse test, t ≤300 μs, duty cycle d ≤ 2 %				

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) Min.	Typ.	Max.	
g_{fs}	V_{DS}= 10 V; I_D = 0.5 I_{D25}, pulse test	45	65		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		4700		pF
C_{oss}			1850		pF
C_{rss}			600		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 60 A R_G = 4 Ω (External)		35		ns
t_r			50		ns
$t_{d(off)}$			85		ns
t_f			26		ns
$Q_{g(on)}$	V_{GS}= 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		155		nC
Q_{gs}			33		nC
Q_{gd}			85		nC
R_{thJC}				0.25	°C/W
R_{thCS}	(TO-3P)		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			140	A
I_{SM}	Repetitive			300	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, Pulse test, t ≤300 µs, duty cycle d≤ 2 %			1.5	V
t_{rr}	I_F = 25 A, -di/dt = 100 A/µs		120		ns
Q_{RM}	V_R = 50 V, V_{GS} = 0 V		2.0		µC

TO-3P (IXTQ) Outline



1 – GATE
2 – DRAIN (COLLECTOR)
3 – SOURCE (EMITTER)
4 – DRAIN (COLLECTOR)

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.185	.193	4.70	4.90
A1	.051	.059	1.30	1.50
A2	.057	.065	1.45	1.65
b	.035	.045	0.90	1.15
b2	.075	.087	1.90	2.20
b4	.114	.126	2.90	3.20
c	.022	.031	0.55	0.80
D	.780	.799	19.80	20.30
D1	.665	.677	16.90	17.20
E	.610	.622	15.50	15.80
E1	.531	.539	13.50	13.70
e	.215 BSC		5.45 BSC	
L	.779	.795	19.80	20.20
L1	.134	.142	3.40	3.60
øP	.126	.134	3.20	3.40
øP1	.272	.280	6.90	7.10
S	.193	.201	4.90	5.10

TO-268 (IXTT) Outline





SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

Fig. 1. Output Characteristics @ 25ºC



Fig. 2. Extended Output Characteristics @ 25ºC



Fig. 3. Output Characteristics @ 150ºC



Fig. 4. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Junction Temperature



Fig. 5. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Drain Current



Fig. 6. Drain Current vs. Case Temperature



Fig. 7. Input Admittance



Fig. 8. Transconductance



Fig. 9. Source Current vs. Source-To-Drain Voltage



Fig. 10. Gate Charge



Fig. 11. Capacitance



Fig. 12. Forward-Bias Safe Operating Area



Fig. 13. Maximum Transient Thermal Resistance