

High Current Ferrite Bead


BPH853025R5-101T

1. Features


- 100% Lead(Pb) & Halogen-Free and RoHS compliant.
- Operating temperature -40~+125°C (Including self - temperature rise)



2. Dimension



CORE SIZE			
A(mm)	B(mm)	C(mm)	D(mm)
8.50±0.25	3.00±0.15	2.50±0.15	1.50±0.15



PRODUCT SIZE				
A(mm)	B(mm)	C(mm)	D(mm)	E(mm)
9.00±0.40	3.00±0.15	2.80±0.25	1.50±0.50	1.25±0.20

3. Part Numbering

BPH
853025
R5
-
101
T

A: Series
 B: Dimension
 C: Material
 D: Impedance
 E: Packaging

Ferrite Core
 101=100Ω
 T=Taping and Reel

4. Specification

TAI-TECH Part Number	ELECTRICAL REQUIREMENTS 1			ELECTRICAL REQUIREMENTS 2			DCR (mΩ) Max.	Rated Current(A)	
	Impedance (Ω)	Tolerance (%)	Test Frequency (MHz)	Impedance (Ω)	Tolerance (%)	Test Frequency (MHz)		ΔT=40°C TYP.	ΔT=60°C TYP.
BPH853025R5-101T	65	±25	25	100	±25	100	1.00	30(1) 13(2)	40(1) 18(2)


Note:

Rated Current :


(1) : Chroma high current test fixture.

(2) :PCB test fixture (30x45mm copper pattern , 50um copper thickness).

Typical Impedance v.s. Frequency Curve



5. Recommended PC Board Pattern



L(mm)	G(mm)	H(mm)
10.7	4.5	1.5