






D

C

B

A



REVISIONS													
P	LTR	DESCRIPTION									DATE	DWN	APVD
	J3	REVISED PER ECO-13-019174									06DEC2013	KH	DR
	J4	REVISED PER ECO-17-016703									02APR2018	RS	DR

1

MATERIAL:
TERMINAL:COPPER (ASTM B152)
RING: ALUMINUM(ASTM B209)
INSULATION: PTFE (ASTM D3295)

2

FINISH:
GOLD PL ASTM B488 TYPE I 0.0013[.000050]
MIN THK OVER NICKEL PL (SAE AMS QQ-N-290) 0.00076[.000030] MIN EXT THK

3 FOR WIRE INS DIA SEE TABLE

4 TONGUE MATERIAL THK: 1.22±0.08[.048±.003]

5 NOTE DELETED

6 NOTE DELETED

9.12 [.359]	23.72 [.934]	4.37 [.172]	7.52 [.296]	328601	1	22.35 [.880]	8.28 [.326]	5.46-6.48 [.215-.255]	329626	11.91 [.469]	39.62 [1.560]	5.00±0.08 [.197±.003]	10	8	329580
F	E	G	C	BODY	BUSHING REQD	H	D	INSUL DIA	SLEEVE ASSY	B	A	ØH	STUD	SIZE	ASSY NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.20[.008]
4 PLC ± -
ANGLES ± -
FINISH

1

2 5

DWN 13APR13
CHK 13APR13
APVD 13APR13

KIRAN HOLAL

ROHDE DANIEL

ROHDE DANIEL

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV J4

TE Connectivity Ltd.

WIRE TERMINAL ASSY,
POST INSULATED, STRATO-THERM
HEAT RESISTANT, 8 AWG

SIZE A2
CAGE CODE 00779
DRAWING NO C-329580

RESTRICTED TO -

1471-9 (1/15)