



CIRCUIT: DPDT


SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	OFF	DN
2-3,5-6	OPEN	2-1,5-4

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4VA @20V AC or DC max.
5. ELECTRICAL LIFE: 40,000 make-and-break cycles at full load.
6. INSULATION RESISTANCE: 1,000M ohm min.
7. DIELECTRIC STRENGTH: 1000V RMS @sea level
8. OPERATING TEMP.: -30°C to 85°C
9. 2002/95/EC (ROHS) COMPLIANT
10. CONTACT MATERIAL: GOLD



VIEW A-A



C	17417	FIXED RATING GOLD	6/27/07	TN
B	15474	CHANGED NOTE 9	10/28/05	PH
A	13037	RELEASED FOR PRODUCTION	4/11/03	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
TITLE				
100DP3T8B13M1RE				
SCALE				
2:1				
DATE				
6/27/07				
DR				
TN				
DWG				
T102315				
REV				
C				