

D

C

B


A

D


C

B

A





SEE TABLE FOR
OF ROWS




A B C D E


PIN PATTERN



- 1 HOUSING MATERIAL: POLYESTER PBT,MOLDING COMPOUND, FLM RTD, 20% GLASS FILLED, COLOR:BLACK.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS C51100, TEMPER H04
- 3 CONTACT FINISH:
MATING SURFACE- 0.0008 MIN GOLD OVER 0.0013 MIN NICKEL.
ON LEADS- 0.0005 MIN TIN-LEAD OVER 0.0013 MIN NICKEL.



0.6±0.05 DIA
⌀ 0.1 (M)
PLATED THROUGH
HOLE
CC PLC



RECOMMENDED PCB
PATTERN

OBSOLETE	125	48	49.88	25	2-636120-2
	120	46	47.88	24	2-636120-1
	115	44	45.88	23	2-636120-0
	110	42	43.88	22	1-636120-9
	105	40	41.88	21	1-636120-8
OBSOLETE	100	38	39.88	20	1-636120-7
	95	36	37.88	19	1-636120-6
	90	34	35.88	18	1-636120-5
	85	32	33.88	17	1-636120-4
	80	30	31.88	16	1-636120-3
	75	28	29.88	15	1-636120-2
	70	26	27.88	14	1-636120-1
	65	24	25.88	13	1-636120-0
	60	22	23.88	12	636120-9
	55	20	21.88	11	636120-8
	50	18	19.88	10	636120-7
	45	16	17.88	9	636120-6
	40	14	15.88	8	636120-5
	35	12	13.88	7	636120-4
	30	10	11.88	6	636120-3
	25	8	9.88	5	636120-2
	20	6	7.88	4	636120-1
CC		BB	AA	ROWS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SMITH 6-30-97	 TE Connectivity Ltd.			
		CHK C.ADAMS 6-30-97				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APP'D T.SMITH 6-30-97	NAME HEADER,2mm HM		
		0 PLC ± 0.1	PRODUCT SPEC — APPLICATION SPEC — —	RESTRICTED TO		
		1 PLC ± 0.1				
		2 PLC ± 0.1				
		3 PLC ± 0.1				
4 PLC ± 0.1	ANGLES ± 0.1	SIZE A1				
MATERIAL		FINISH	WEIGHT 0.000000	CAGE CODE 00779	DRAWING NO C636120	
 			CUSTOMER DRAWING			
			SCALE 5:1	SHEET 1 OF 1	REV D	