

## Coaxial Cable Connector 25\_N-50-2-14/133\_N

### Description

Straight panel cable jack, flange mount

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0427 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00009332
Assembly instruction	DOC-0000182188
Mounting hole	DOU-00008795

### Ordering Information

Single package	25_N-50-2-14/133_NE
----------------	---------------------

### Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86
-----------------	---------------------------