


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED AS PER ECO-20-003569.	11MAR2020	TC	NP



NOTES:

1. PART DESCRIPTION: CONNECTOR, JACK, TRIAXIAL, BULKHEAD (RAYTHEON # 1145047) COMPLETE WITH PREFLUXED SOLDER PREFORM RING AND HEAT SHRINKABLE INSULATING SLEEVE.

MATERIAL:

HOUSING BODY: BRASS ALLOY PER ASTM B16 (QQ-B-626)
 JAM NUT: BRASS ALLOY PER ASTM B16 (QQ-B-626)
 INSULATING SLEEVE: HEAT SHRINKABLE, POLYVINYLIDENE FLUORIDE (TRANSPARENT BLUE)
 SOLDER RING: PREFLUXED SOLDER PREFORM, COMPOSITION Sn63, ROLO FLUX PER ANSI-J-STD-004.
 INSULATOR: THERMOPLASTIC PER LP 392.

FINISH:

HOUSING BODY: TIN PLATED PER MIL-T-10727
 JAM NUT: NIQUEL PLATED PER QQ-N-290
 LOCK WASHER: PASSIVATED PER MIL-S-5002

2. HOUSING ACCOMMODATION: HOUSING DESIGNED TO ACCEPT SHIELDED CONTACTS MIS-20067/1 THRU MIS-20067/4 SHIELDED, RAYCHEM SOLDER TACT D-602-44/45 AND D-602-54/55.
 3. WIRE SIZE: HOUSING WILL TERMINATE OUTER SHIELD OF TRIAX/ TWINAX CABLE HAVING A SHIELD DIA. OF .185 MAX.
 4. MATING CONNECTORS: THIS CONNECTOR WILL MATE WITH D-621-0001 (RAYTHEON# 11453046) CONNECTOR, PLUG SUBMINIATURE, TRIAXIAL.

5. ITEMS SUPPLIED AS PART OF CONNECTOR ASSEMBLY.
 6. JAM NUT AND LOCKING WASHER SUPPLIED UNASSEMBLED.
 7. RECOMMENDED TWINAX STRIPPING TOOL AD-1479 OR AD-1496.
 8. SEE PROCEDURE ES 61124 FOR TERMINATION INFORMATION.

MOUNTING HOLE

ACCESSORIES 5. 8.


CTA-0012	BARRIER TUBE
CTA-0013	PREFORM INSULATOR SLEEVES (2)
D-600-0024	STRAIN RELIEF

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.01
3 PLC	± 0.005
4 PLC	± -
ANGLES	± -



DWN T.CORREIA 11MAR2020

CHK R.MACNAUGHTON 11MAR2020

APVD N.PRZYBYLSKA 11MAR2020

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 0.000000

MATERIAL

FINISH



TE Connectivity

NAME

CONNECTOR, JACK
TRIAXIAL, BULKHEAD

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

06090

C-D-621-0002

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 1

REV

F