








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16APR2015	DL	CW
	B	ECR-21-111798	06OCT2021	WQR	CW
	BI	ECR-22-127614	27JAN2022	WQR	CW




SCALE 1:1

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50V
RATED CURRENT: 1A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 0.8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 750
OPERATION TEMPERATURE: $-40^{\circ}C \sim +70^{\circ}C$

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 1A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 0.8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 750
工作温度: $-40^{\circ}C \sim +70^{\circ}C$



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 16APR2015	TE Connectivity								
		CHK CHRIS WANG 16APR2015									
DIMENSIONS: mm		APVD XU XIANG 16APR2015	NAME HMN-RJ45-F								
		PRODUCT SPEC 108-137065									
		APPLICATION SPEC 114-137065									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -	SIZE A3		CAGE CODE -		DRAWING NO C-T2113000201000		RESTRICTED TO		
MATERIAL - -		FINISH - -	CUSTOMER DRAWING								
			SCALE 2:1		SHEET 1		OF 1		REV B1		