





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REV PER ECR-14-016951	11FEB2015	I.T	W.H



1. HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, COLOR; BLACK.
CONTACT MATERIAL: PHOSPHOR BRONZE.
2. CONTACT FINISH: NICKEL UNDERPLATE ALL OVER, MATING SURFACES PLATED TO MEET PLI PERFORMANCE REQUIREMENTS OF INDUSTRY SPECIFICATION EIA-700AAAB, SOLDER TAILS PLATED TIN-LEAD.
3. DATUM LOCATIONS AND BASIC DIMENSIONS TO BE ESTABLISHED BY THE CUSTOMER. CONSULT AMP ENGINEERING WHEN PLACING MULTIPLE CONNECTORS ON A PC BOARD.
4. PACKAGED IN TAPE ON REEL PER EIA-481.
5. 1.5 MIN DIAMETER HOLE SHOULD BE USED IF USING POST STYLE "A" AND PLACING ON PCB WITH VACUUM PLACEMENT EQUIPMENT.
6. SHORTER SOLDER LANDS MAY BE USED PER EIA 700AAAB, HOWEVER 2.7 LENGTH ASSURES OPTIMUM SOLDER FILLET REGARDLESS OF MANUFACTURER OF CONNECTOR.
7. REFERRED TO AS DIM N IN EIA 700AAAB SPECIFICATION.
8. CONTACT FINISH: 0.002 MINIMUM BRIGHT TIN-LEAD (93-7) ON SOLDER AREA, 0.00127 MINIMUM GOLD ON MATING AREA, BOTH OVER 0.00127 MINIMUM NICKEL ON ENTIRE CONTACT.
- OBsolete PART NUMBER.
9. SQUARE AND DIAMOND SHAPED POSTS
10. ROUND SHAPED POSTS



STYLE A POST



STYLE B POST



RECOMMENDED PC BOARD LAYOUT

POST STYLE	FINISH	DIM D	DIM C	DIM B	DIM A	STACK HGTS	POS	PART NO
1	8	44.4	45.9	44.58	41	9,11,14	84	3-120526-2
1	8	34.4	35.9	34.58	31	9,11,14	64	3-120526-1
1	2	44.4	45.9	44.58	41	9,11,14	84	2-120526-2
1	2	34.4	35.9	34.58	31	9,11,14	64	2-120526-1
10	8	44.4	45.9	44.58	41	9,11,14	84	1-120526-2
10	8	34.4	35.9	34.58	31	9,11,14	64	1-120526-1
9	10	44.4	45.9	44.58	41	9,11,14	84	120526-2
10	2	34.4	35.9	34.58	31	9,11,14	64	120526-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	2/11/97		 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	2/11/97			
DIMENSIONS:		1.0mm		NAME		
		PRODUCT SPEC		PLUG ASSY, 1.0mm FH(IEEE1386) CONNECTOR		
0.0125		502-1079				
0.0125		APPLICATION SPEC		SIZE		
0.0125		114-25045				
0.0125		WEIGHT		CAGE CODE		
0.0125		CUSTOMER DRAWING				
0.0125		SCALE		DRAWING NO		
0.0125		10:1				
0.0125		SHEET		RESTRICTED TO		
0.0125		1 OF 1				
0.0125		REV		G		
0.0125		G				