



|           |           |
|-----------|-----------|
| O.P. (MM) | P.T. (MM) |
| 10.9±1.0  | 3.2 MAX.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X  $\pm$  0.4  
X.XX  $\pm$  0.25
3. RATING: 5A @125/250VAC UL, CUL, VDE APPROVED
- ▲ 4. OPERATING FORCE: 20 $\pm$  10 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. 2002/95/EC (ROHS) COMPLIANT
12. ▲ DENOTES CRITICAL PARAMETER.

|     |        |                         |         |     |
|-----|--------|-------------------------|---------|-----|
| B   | 22330  | correct Actuator length | 5/26/16 | MW  |
| A   | 21129  | RELEASED FOR PRODUCTION | 5/14/13 | EBP |
| REV | PCR NO | DESCRIPTION             | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



**E♦SWITCH®**

TITLE MS0850504F020C1C

SCALE 2:1

DATE 5/14/2013

|    |     |
|----|-----|
| DR | EBP |
|----|-----|

DWG  
Q970133

REV  
B