




REV. 1 3/27/96

COIL: @ 25°C

RESISTANCE 3300 OHMS $\pm$ 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 15.2 VDC

MUST RELEASE 10.8 VDC MAX, 1.7 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 7.5 MS MAX

CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/25/96 CK 3/27/96

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M39016/21-046M

TYPE JMSDD RELAY

JMSCDD-26XMS