




P.C.B LAYOUT



N=Number of contacts



SIGN	DATE	DESCRIPTION	APPROVER
△	09/16/09	Poles is changed from 2p-24p to 4p-24p	Aaron
△	09/16/09	Drawing NO. is changed from 8VI0137 to 8VI0302	Aaron
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing: Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"- "slot type

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 16A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

VI xx 21 x 5 xxxx G			
△ 04	4 CONTACTS	0 Black	0000:"@ "Logo (Standard)
05	5 CONTACTS	5 Green	000A:"ANYTEK"Logo
...	...	6 Blue	Any special item by
24	24 CONTACTS	8 Light Grey	customer request,
			please contact sales
			department.

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A			20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
Dim B			15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.10				±0.15				±0.20			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.20		±0.25				±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VI 5.08 SERIES 4P-24P 180° wire inlet (without cover) Horizontal-solid block 					
PART NO.	Vlxx21x5xxxxG			DWG NO.	8VI0302 	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Aaron 2009.09.16	Aaron 2009.09.16	 	UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: C	X.XX ±0.10