





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECR-21-100678	08APR2021	SS	VS

- 1 APPLICABLE WIRE RANGE: 18AWG COPPER STRANDED
- 2 APPLICABLE INSULATION DIAMETER: 2.40-3.30mm.
2.00-3.30mm WHEN AN OVERLAP INSULATION APPLICATOR IS USED.
- 3 APPLICABLE MATED PLUG HOUSING P/N:
-1971773-/*-1971776-*/*-1971876-*/
-2232265/*-2232266-*/*-2232357-*

△ WIRE SIZE INDICATOR "D"=18 AWG

COPPER ALLOY	HIGH (150°C)	M0-D	2238066-2
PHOS BRONZE	STANDARD (105°C)	M1-D	2238066-1
MATERIAL	TEMP. RATING	△ MATERIAL/SIZE MARK	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17NOV2014 NAGALAKSHMI K CHK 17NOV2014 JACON. GENE APVD 17NOV2014 JACON. GENE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ±0.5 2 PLC ±0.30 3 PLC ± 4 PLC ± ANGLES ± FINISH PRE-TIN		RECEPTACLE CONTACT POWER TRIPLE LOCK, 18 AWG	
MATERIAL SEE TABLE		PRODUCT SPEC 108-106118 APPLICATION SPEC 114-106118 WEIGHT -		SIZE A2	CAGE CODE 00779
		Customer Drawing		DRAWING NO C=2238066	RESTRICTED TO -
				SCALE 10:1	SHEET 1 OF 1
					REV D